

Product Description

Mixed assembly guarantees a high flexibility.



Benefits

- Mixed assembly guarantees a high flexibility.

Product features

- MCR Frame version "male" is designed for usage with modules with male contacts, version "female" is designed for usage with modules with female contacts

Cross-References

Suitable housing:

EPIC® H-B 16 TG-RO, EPIC® H-B 16 TGH-RO, EPIC® H-B 16 TS-RO, EPIC® H-B 16 TSH-RO, EPIC® H-B 16 TG, EPIC® H-B 16 TG 2X, EPIC® H-B 16 TGH, EPIC® H-B 16 TGH 2X, EPIC® H-B 16 TGB, EPIC® H-B 16 TGBH, EPIC® H-B 16 TS, EPIC® H-B 16 TSH, EPIC® H-B 16 TSB, EPIC® H-B 16 TSBH, EPIC® H-B 16 AG-LB, EPIC® H-B 16 AD-LB, EPIC® H-B 16 AG, EPIC® H-B 16 AD-BO, EPIC® H-B 16 SGR-LB, EPIC® H-B 16 SGRL-LB, EPIC® H-B 16 SGRH-LB, EPIC® H-B 16 SGRLH-LB, EPIC® H-B 16 SDR-LB, EPIC® H-B 16 SDRL-LB, EPIC® H-B 16 SDRH-LB, EPIC® H-B 16 SDRLH-LB, EPIC® H-B 16 SGR, EPIC® H-B 16 SGRL, EPIC® H-B 16 SGRH, EPIC® H-B 16 SGRLH, EPIC® H-B 16 SDR-BO, EPIC® H-B 16 SDRL-BO, EPIC® H-B 16 SDRH-BO, EPIC® H-B 16 SDRLH-BO, EPIC® H-B 16 TBF-LB, EPIC® H-B 16 TBFH-LB, EPIC® H-B 16 TBF, EPIC® H-B 16 TBFH, EPIC® H-B 16 TSH-ZB, EPIC® H-B 16 AG-ZR

Suitable inserts

EPIC® MC Module: High Current 1+PE, EPIC® MC Module: High Current 2pole, EPIC® MC Module: High Voltage 3pole, EPIC® MC Module: High Voltage 4+PE, EPIC® MC Module: 3pole, EPIC® MC Module: HE 4pole, EPIC® MC Module: Cage clamp 4pole, EPIC® MC Module: 5pole, EPIC® MC Modul: 10pole, EPIC® MC Module: 10pole, EPIC® MC Module: 20pole, EPIC® MC Module: Koax 3pole, EPIC® MC Module: PROFIBUS DP, EPIC® MC Module: Universal Bus, EPIC® MC Module: RJ45, EPIC® CE6326 Connector RJ45, EPIC® MC Module Pneumatic 1pole,



EPIC® MC Module Pneumatic 2pole, EPIC® MC Dummy Module, EPIC® MC Module removal tool

Article List

Part number	Part	Number of modules	Version	Pieces / PU
MCR 16 frame				
10381400	MCR 16 S	5	male	5
10381500	MCR 16 B	5	female	5