

SwitchLine

Accessories

Ordering information



OA_G_




OTZC_




OTS_L




OTS_S




OZXB2K




OZXB3K



OZXB4K



OZXB5K



OETLZW_

Auxiliary contact blocks

Mounting on the right side of the switch: Max. 4 auxiliary contact blocks/switch (totally 8 blocks). Simultaneous action with the main contacts.

Function	Protection degree	Type	Order number	Weight [kg]
1NO	IP20	OA1G10	1SCA022353R4970	0.03
1NC	IP20	OA3G01	1SCA022456R7410	0.03

Bridging bars

The bridging bars provide a connection link either on the incoming or outgoing side of the switch.

Suitable for switches	Number of poles	Type	Order number	Weight [kg]
OT160...250 E_C	3	OTZC13	1SCA022767R6910	0.60
	4	OTZC14	1SCA022767R7040	0.80
OT315...400 E_C	3	OTZC23	1SCA022767R7120	0.60
	4	OTZC24	1SCA022767R7210	0.80
OT630...800 E_C	3	OTZC33	1SCA022785R7020	1.00
	4	OTZC34	1SCA022785R7110	1.30

Terminal shrouds

Snap-on mounting, grey plastic. Transparent shrouds available on request, please replace the letter "G" with "T". Suitable for the upper switch. A kit includes three (four) shrouds which can be used on either side of the switch.

Suitable for switches	Number of poles	Description	Type	Order number	Weight [kg]
OT160...250	3	Long type	OTS250G1L/3	1SCA022731R8150	0.09
	3	Short type	OTS250G1S/3	1SCA022731R8310	0.06
OT160...250	4	Long type	OTS250G1L/4	1SCA022731R8230	0.12
	4	Short type	OTS250G1S/4	1SCA022731R8400	0.08
OT315...400	3	Long type	OTS400G1L/3	1SCA022736R8840	0.15
	3	Short type	OTS400G1S/3	1SCA022736R9060	0.09
OT315...400	4	Long type	OTS400G1L/4	1SCA022736R9490	0.20
	4	Short type	OTS400G1S/4	1SCA022736R9650	0.12
OT630...800	3	Long type	OTS800G1L/3	1SCA022776R7890	0.32
	3	Short type	OTS800G1S/3	1SCA022776R8190	0.17
OT630...800	4	Long type	OTS800G1L/4	1SCA022776R7970	0.42
	4	Short type	OTS800G1S/4	1SCA022776R8270	0.26

Snap-on mounting, transparent plastic, IP 2X.

Suitable for terminal clamps	Number of poles	Type	Order number	Weight [kg]
OZXB2, 2L	3	OZXB2K	1SCA022264R0010	0.05
OZXB3, 4	3	OZXB3K	1SCA022264R0440	0.20
OZXB5, 6	3	OZXB4K	1SCA022199R2850	0.24
OZXB7, 7L	3	OZXB5K	1SCA022283R8040	0.13

Locking accessories

Cam attachment for adopting the switches to Castell, Lowe&Fletcher or Ronis interlock. The lock is not included. Mounting to OXP-shaft, works together with OH-door handle and a shaft.

Suitable for switches	Type	Order number	Weight [kg]
OT160...250E_C	OETLZW16	1SCA022093R2070	0.17
OT315...800E_C	OETLZW5	1SCA022052R3900	0.14