

Kingston CompactFlash Ultimate

kingston.com/flash

flash

The ultimate card for ultimate performance.



Advanced amateurs and professional photographers need Flash memory they can count on for even the most demanding shoots. That's why Kingston® enhanced our CompactFlash® Ultimate cards. The newly redesigned Kingston CompactFlash Ultimate offers an amazing minimum sustained write speed rating of 266X, making it our fastest card to support high-end digital cameras and devices. It's designed to work with Windows® 7 and deliver superior results with fast data transfer and support for continuous shooting.

With its ultra-fast transfer rates of 45MB/sec. read and 40MB/sec. write, you can capture more continuous, high-resolution images in less time with the CompactFlash Ultimate than traditional CompactFlash memory cards. For added peace of mind, CompactFlash Ultimate comes with a bonus download for data recovery software from MediaRECOVER®. With MediaRECOVER, you can recover lost or deleted files and restore corrupt files on Windows or Mac systems.

To ensure that Kingston Flash memory solutions are among the performance leaders in their class, Kingston engineers select high-performance controllers as part of each card's design. Each card is 100-percent tested and you can rest assured that every CompactFlash Ultimate card has received a perfect score.

Available in capacities up to 32GB*, CompactFlash Ultimate offers plenty of room for capturing and storing high volumes of images in RAW, JPEG, TIFF and other large file formats. As with all Kingston Flash cards, CompactFlash Ultimate cards are backed by a lifetime warranty, 24/7 live technical support and the legendary reliability that makes Kingston the leader in memory.

Optional Accessories

- FCR- HS219/1 – Media Reader

Features/Specifications

- **Capacities*** — 16GB, 32GB
- **Dimensions** — 1.43" x 1.68" x 0.13" – CF Type I (36.4 mm x 42.8 mm x 3.3 mm)
- **Speed Rating**** — 45MB/sec. read, 40MB/sec. write
- **Recovery Utility** — data recovery software download from MediaRECOVER Windows/Mac compatible
- **Operating Temperature** — 32° F to 140° F (0° C to 60° C)
- **Storage Temperature** — -4° F to 185° F (-20° C to 85° C)
- **Standardized** — complies with CompactFlash Association specification standards
- **Easy** — plug and play
- **Economical** — autosleep mode preserves system battery life
- **Guaranteed** — lifetime warranty

Kingston part numbers:

CF/16GB-U2†; CF/32GB-U2†

	Media Recover
Windows 7/2000/XP/Vista®	✓
Mac OS X v. 10.3.x +	✓

* Please note: Some of the listed capacity is used for formatting and other functions and thus is not available for data storage. For more information, please consult Kingston's Flash Memory Guide at kingston.com/Flash_Memory_Guide.

** Speed may vary due to host and device configuration.

† CompactFlash Ultimate 16GB and higher cards work in newer cameras and other devices that are capable of utilizing a FAT32 file system. PRODUCT SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

©2010 Kingston Technology Corporation, 17600 Newhope Street, Fountain Valley, CA 92708 USA.

All rights reserved. All trademarks and registered trademarks are the property of their respective owners. Printed in the USA MKD-115.2

