

Labels That Stick and Last



RhinoPRO™ Labels

Portable label printers are only as good as the labels on which they print. That's why DYMO designed a series of labels for a multitude of applications on a wide variety of surfaces. Designed to work with the DYMO RhinoPRO series of portable label printers, these labels will stick and stay stuck.

- Easy to peel, split back labels
- Permanent adhesive results in labels that stick and last in heavy duty environments.
- Thermal transfer print technology is durable, smear proof, chemical and solvent resistant

Flexible Nylon

The principal application for RhinoPRO labels is wire and cable wraps. The flexible nylon labels are made of memory-resistant materials, making them ideal to wrap around curved surfaces – wire and cable – and the adhesive will stick and stay stuck for the lifetime of the cable. Don't try this with ordinary office labels, they'll quickly fall to the floor.



Permanent Polyester

Featuring a "shinier" finish than the Flexible Nylon, the RhinoPRO Permanent Polyester tape presents a more sophisticated look and is designed for flat surfaces. Ideal for patch panels, racks, enclosures, factory equipment and much more.




Metallized Permanent Polyester

For an even more polished finish, choose the Metallized Permanent Polyester labels. Fashioned with a unique metallic silver finish, these labels are great for asset tagging, face plates, factory equipment, tool bins, and anywhere you'd use a flat –surface label.



Heat Shrink Tubes

Specifically designed for all applications that require normal heat shrink tubing. The cassette fits into all RhinoPRO printers. Made of industrial grade polyolefin and featuring a 3:1 heat shrink ratio, these new labels offer the convenience of printing directly on the tubing itself – eliminating the need for an extra labeling step.



How do you sign
YOUR work?™



RhinoPRO™ Labels



PICKING THE RIGHT LABEL FOR YOUR APPLICATION

Surface Applications	Examples	Environment	Label Type	Available Sizes
Smooth/Flat/Textured/ Highly Textured	Factory equipment, bins, machinery, patch panels, electrical panels, etc	Factory floors, electrical rooms, telecom rooms, office	RhinoPRO Permanent Polyester Labels	3/8", 1/2", 3/4"
Wire/Cable/Curved/Smooth/ Flat/Textured/Highly Textured	Electrical cables, datacom cables, pipes, factory equipment, bins, machinery, patch panels, electrical panels, etc	Factory floors, electrical rooms, telecom rooms, office	RhinoPRO Flexible Nylon Labels	1/2", 3/4"
Wire/Cable	Electrical cables, datacom cables	Factory floors, electrical rooms telecom rooms, office	RhinoPRO Polyolefin Heat Shrink Tube	1/4", 3/8", 1/2", 3/4"

LABEL SELECTION CHART

Part#	Product Description	Length	RhinoPRO 5000	RhinoPRO 3000	RhinoPRO 1000
18482	White Perm Poly Tape 3/8" (9mm)	18'	✓	✓	✓
18483	White Perm Poly Tape 1/2" (12mm)	18'	✓	✓	✓
18484	White Perm Poly Tape 3/4" (19mm)	18'	✓	✓	✓
18485	Metallized Perm Poly Tape 3/8" (9mm)	18'	✓	✓	✓
18486	Metallized Perm Poly Tape 1/2" (12mm)	18'	✓	✓	✓
18487	Metallized Perm Poly Tape 3/4" (19mm)	18'	✓	✓	✓
18488	White Flexible Nylon Tape 1/2" (12mm)	11.5'	✓	✓	✓
18489	White Flexible Nylon Tape 3/4" (19mm)	11.5'	✓	✓	✓
18490	Yellow Flexible Nylon Tape 1/2" (12mm)	11.5'	✓	✓	✓
18491	Yellow Flexible Nylon Tape 3/4" (19mm)	11.5'	✓	✓	✓
New! 18051	White Heat Shrink Tube 1/4" (6mm)	5'	✓	✓	✓
18052	Yellow Heat Shrink Tube 1/4" (6mm)	5'	✓	✓	✓
18053	White Heat Shrink Tube 3/8" (9mm)	5'	✓	✓	✓
18054	Yellow Heat Shrink Tube 3/8" (9mm)	5'	✓	✓	✓
18055	White Heat Shrink Tube 1/2" (12mm)	5'	✓	✓	✓
18056	Yellow Heat Shrink Tube 1/2" (12mm)	5'	✓	✓	✓
18057	White Heat Shrink Tube 3/4" (19mm)	5'	✓	✓	✓
18058	Yellow Heat Shrink Tube 3/4" (19mm)	5'	✓	✓	✓

For more information or the name of a
DYMO Industrial distributor, please visit
www.dymo.com/industrial
or call us at
1-800-426-7827



**How do you sign
YOUR work?™**



USA contact: DYMO Corporation, 44 Commerce Road, Stamford, CT 06902-4561
Canada contact: Esselte Corporation, 333 Foster Crescent, Suite 2, Mississauga, Ontario L5R 3Z9 Canada • 1-800-263-6105
© 2005 DYMO Corporation. DYMO is a registered trademark of Esselte Corporation. RhinoPRO is a trademark of Esselte Corporation.