



Capsuleline

Capsuleline 20W G4 24V CL 4000h 1CT

Single-ended low-voltage halogen capsule giving crisp white halogen light

Product data

• General Characteristics

Philips Code	13091
Cap-Base	G4
Cap-Base Information	na [-]
Bulb	T3 [T3: .354 inch / 9 mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Nominal Lifetime	4000 hr
Rated Lifetime	4000 hr
Rated Lifetime (years)	4 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	3000 K
Colour Temperature Technical	3000 K
Lamp Luminous Flux	300 Lm
Rated Luminous Flux	300 Lm
Lamp Luminous Efficacy	15 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	20.0 W
Lamp Wattage	20 W
Technical Lamp Power	20.0 W
Power Factor	1 -
Voltage	24 V
Lamp Current	0.83 A
Dimmable	yes
Starting Time	0.0 s

Warm-up Time to 60% Light Outp	instant full light
--------------------------------	--------------------

• Environmental Characteristics

Energy Efficiency Label (EEL)	C
Energy consumption kWh/1000h	21 kWh

• Measuring Conditions

Switching cycle	16000X
-----------------	--------

• Luminaire Design Requirements

Pinch Temperature	350 (max) C
Bulb Temperature	900 (max) C

• Product Dimensions

Overall Length C	33 (max) mm
Diameter D	9 (max) mm
Light Center Length L	24 mm

• Product Data

Order code	409621 50
Full product code	871150040962150
Full product name	Capsuleline 20W G4 24V CL 4000h 1CT
Order product name	Caps 20W G4 24V CL 4000h 1CT/ 10X10F
Pieces per pack	1
Packing configuration	10X10F
Packs per outerbox	100


PHILIPS

Capsuleline

Bar code on pack - EAN1 8711500409621
Bar code on intermediate packing - EAN2 8711500422613
Bar code on outerbox - EAN3 8711500425706


Logistic code(s) - 12NC 924038820501
ILCOS code HSG/C-20-24-G4
Net weight per piece 1.200 gr

Dimensional drawing



Capsuleline 20W G4 24V CL 4000h 1CT

Product	C (Max)	D (Max)	L (Norm)
CAP ST 13091 20W G4 24V CL	33	9	24



G4



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 17
data subject to change