

## HOLE SAWS AND ARBORS

### HOLE SAWS 3201

Professional quality HSS bi-metal hole saws with vari-pitch teeth for fast clean cutting. Ideal for cutting clean holes in steel, stainless steel, die cast metals, nail embedded wood, hardwood floors, plywood, plastics etc. Display packed.



SIZE	ITEM NO	BOX QTY	WEIGHT
16mm/5/8"	T3201 016	1	31g
19mm/3/4"	T3201 019	1	32g
20mm/7/8"	T3201 020	1	40g
21mm/13/16"	T3201 021	1	37g
22mm/7/8"	T3201 022	1	50g
25mm/1"	T3201 025	1	60g
29mm/1 1/8"	T3201 029	1	80g
32mm/1 1/4"	T3201 032	1	88g
35mm/1 3/8"	T3201 035	1	104g
38mm/1 1/2"	T3201 038	1	120g
40mm/1 5/8"	T3201 040	1	130g
41mm/1 5/8"	T3201 041	1	140g
43mm/1 7/8"	T3201 043	1	90g
44mm/1 3/4"	T3201 044	1	95g
48mm/1 7/8"	T3201 048	1	110g
51mm/2"	T3201 051	1	128g
54mm/2 1/8"	T3201 054	1	140g
57mm/2 1/4"	T3201 057	1	150g
60mm/2 3/8"	T3201 060	1	170g
64mm/2 1/2"	T3201 064	1	190g
65mm/2 5/8"	T3201 065	1	195g
67mm/2 5/8"	T3201 067	1	200g
68mm/2 1/4"	T3201 068	1	115g
70mm/2 3/4"	T3201 070	1	220g
73mm/2 5/8"	T3201 073	1	240g
76mm/3"	T3201 076	1	260g
79mm/3 1/8"	T3201 079	1	198g
83mm/3 1/4"	T3201 083	1	229g
86mm/3 3/8"	T3201 086	1	230g
89mm/3 1/2"	T3201 089	1	250g
92mm/3 5/8"	T3201 092	1	270g
95mm/3 3/4"	T3201 095	1	280g
102mm/4"	T3201 102	1	340g
105mm/4 1/8"	T3201 105	1	355g
111mm/4 3/8"	T3201 111	1	385g
114mm/4 1/2"	T3201 114	1	410g

**CONTACT NOS:**  
**IRELAND** Tel: +353 (0) 1•8851669  
 Fax: +353 (0) 1•8851670 dublin-sales@ck-tools.com  
**FRANCE** No. azur +33 (0) 810•000044 Fax: +33 (0) 810•000357  
**USA** Tel: +1 866 484 5943 Fax: +1 630 953 2686 CKUSANICK@aol.com  
**GERMANY** Tel: +49 (0) 202•89030 Fax: +49 (0) 202•80715 info@ck-tools.de

### 6 PIECE HOLE SAW SET 3211

6 pieces Set of hole saws in plastic case.

CONTENTS:

Hole saws 3201 sizes: 38, 40, 65, 67, 68mm Arbor no. 3207 with pilot drill for hole saws 32 - 111 mm Ø



ITEM NO	BOX QTY	WEIGHT
T3211	1	1348g

### 8 PIECE HOLE SAW SET 3210

8 piece Set of hole saws in plastic case.

CONTENTS:

Hole Saws No. 3201 sizes: 22, 29, 35, 44, 51, 64mm. Arbor 3208 with pilot drill, fixing pins and fixation plate + additional Arbor with screw head 16-30mm and hexagon key 4mm.



ITEM NO	BOX QTY	WEIGHT
T3210	1	285g