


**Ordering number CA12062_EMILY-D**

Family	Emily	FWHM	11 degrees
Type	Assembly	Efficiency	91 %
LED	LUXEON A	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	14.9 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

**Ordering number CA12064_EMILY-M**

Family	Emily	FWHM	18 degrees
Type	Assembly	Efficiency	90 %
LED	LUXEON A	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

**Ordering number CA12070_EMILY-M2**

Family	Emily	FWHM	28,5 degrees
Type	Assembly	Efficiency	90 %
LED	LUXEON A	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

**Ordering number CA12066_EMILY-O**

Family	Emily	FWHM	44+10 degrees
Type	Assembly	Efficiency	(simulated) 0 %
LED	LUXEON A	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		



PRODUCT DATASHEET
Emily series
last update 3/1/2013

PHILIPS
LUMILEDS

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Emily series

last update 3/1/2013

PHILIPS
LUMILEDS

GENERAL INFORMATION

- Product series especially designed & optimized for LUXEON A series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>