



GE  
Lighting



## ConstantColor™ CMH Single Ended CMH150/T/UVC/U/830/G12 **20012**

### Product information

GE's low watt **CMH lamps** have opened new possibilities for lighting design, combining the power and light quality of far larger and less efficient lamps. It is now possible to achieve lighting design that could not be achieved previously with inferior technologies. GE's new **ConstantColor™ CMH Precise™** technology platform has been developed with specific focus to retail applications. GE Precise™ technology offers superb overall light quality, outstanding lumen maintenance, improved efficacy, while maintaining long life and reliability. These qualities are why GE is the leader in ceramic metal halide technology.



WORLDWIDE PARTNER

## Product data

Cap/Base	G12
Bulb Shape	Tubular
Bulb Finish	Clear
Maximum Overall Length [mm]	100
Light Center Length [mm]	56
Net weight per piece [g]	32
Gross weight per piece [g]	42
Operating position	U - Universal
Mercury Content [mg]	11.6
UV radiance	Exempt
Brand	General Electric (GE)

## Performance data

Colour Code	830
Colour Rendering Index (CRI) [Ra]	80
Nominal correlated colour temperature (CCT) [K]	3000
Nominal lumens [lm]	14000
Rated Lumens [lm]	14970
Nominal efficacy [LpW]	93
Rated efficacy [LpW]	102.7
Energy efficiency class (EEC)	A+
Nominal chromaticity coordinate X	0.435
Nominal chromaticity coordinate Y	0.4
Weighted energy consumption [kWh/1000h]	160.27

## Electrical data

Nominal power [W]	150
Rated power [W]	145.7
Nominal lamp voltage [V]	93
Lamp Current [A]	1.9
Design Ambient Temperature [°C]	25
Run-up time (sec)	180
Hot restart time (sec)	900
Dimming Capability	No
Ballast Required	Yes


## Logistic data

DUN Code	20043168200121
EAN Code	0043168200127
Pack Quantity	12
Layer quantity	396 EUR, 504 UK
Layer quantity EUR	396
Layer quantity UK	504
Pallet quantity EUR (PC)	2772
Pallet quantity UK (PC)	3528
Outer case size	186 x 146 x 140 (mm)
Product status	Available


## Application areas



### Lumen maintenance data



### Survival Data



## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[HID Lamps Spectrum Catalogue \(EN\) \(PDF\)](#)

[ConstantColor™ CMH Ultra Brochure \(PDF\)](#)

[ConstantColor™ White Light CMH Brochure \(PDF\)](#)

[ConstantColor™ CMH G12 Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)