

Tool Cabinet with 145 Tools & Inlays



Bahco Tool Trolley & Large Tool Set with Inlays

Heavy duty double wall frame mobile tool cabinet with reinforced design and huge tool set supplied in inlays for easy installation. Ideal for any tradesman.

Soft close system on drawers

Long ball bearing slides with 7 full opening drawers

Specially designed to ensure drawers continue to operate even when the frame is dented or damaged

Round key locking mechanism

125 x 30mm non marking ball bearing wheels

2 fixed and 2 swivel wheels with brake

30kg load capacity per individual drawer

Set Contents:

17 x Combination Spanners: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24 mm
8in Adjustable Spanner
6 x Slotted Screwdrivers: 3 x 60, 3.5 x 70, 4 x 100, 5.5 x 100, 6.5 x 125, 8 x 125mm
2 x Phillips Screwdrivers : PH1 x 75, PH2 x 100mm
2 x Pozidriv Screwdrivers: PZ1 x 75, PZ2 x 100mm
5 x Torx Screwdrivers: T10, T15, T20, T25, T30
Stubby Ratcheting Screwdriver
9 x Ball-End Long Hex Key Set: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm
5 x Pozidriv Bits: PZ1, PZ2 (x3), PZ3
7 x Phillips Bits: PH1, PH2 (x3), PH2 Slim (x2), PH3
11 x Torx Bits: T10, T15 (x3), T20 (x3), T25 (x2), T27, T30
3 x Slotted Bits: 3, 4.5, 5.5mm
4 x Hex Bits: 3, 4, 5, 6mm
Magnetic Bit Holder
Hacksaw Frame
8in Hand Flat File
8in Hand Half Round File
8in Hand Round File
3m Tape Measure
35mm Nylon Tip Mallet
German DIN Hammer, 300g
Wire Brush
9mm Snap Off Blade Knife
10 x Snap Off Blades
1/4in Drive Bit Holder Adaptor
1/4in Drive Adaptor
160mm Side Cutters
160mm Snipe Nose Pliers
250mm Slip Joint Pliers
12 x 1/4in Sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13mm
18 x 1/2in Sockets: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24, 27, 30, 32mm
1/4in Ratchet Handle
1/2in Ratchet Handle
1/4in Sliding T-bar
1/2in T-adaptor
2 x 1/4in Extension Bars ; 75mm, 150mm Flexible