


**UTTB 2,5- 2-BE**

Order No.: 3046757

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=3046757>

Feed-through modular terminal block, Cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 26 - 12, Connection type: Screw connection, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7.5, NS 35/15

**Commercial data**

|                |                                                                                                        |
|----------------|--------------------------------------------------------------------------------------------------------|
| GTIN (EAN)     | <br>4 046356 103725 |
| sales group    | A832                                                                                                   |
| Pack           | 50 pcs.                                                                                                |
| Customs tariff | 85369010                                                                                               |

**Product notes**

WEEE/RoHS-compliant since:  
11/09/2005



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

**Certificates / Approvals**

Certification

CSA, CUL, UL

## Accessories

| Item                | Designation            | Description                                                                                                                                                                                        |
|---------------------|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Assembly</b>     |                        |                                                                                                                                                                                                    |
| 3047316             | ATP-UTTB 2,5/4         | Partition plate, Length: 74.3 mm, Width: 2.2 mm, Height: 70 mm, Color: gray                                                                                                                        |
| 3047293             | D-UTTB 2,5/4           | End cover, Length: 69.9 mm, Width: 2.2 mm, Height: 57.5 mm, Color: gray                                                                                                                            |
| <b>Bridges</b>      |                        |                                                                                                                                                                                                    |
| 3030161             | FBS 2-5                | Plug-in bridge, Number of positions: 2, Color: red                                                                                                                                                 |
| 3030174             | FBS 3-5                | Plug-in bridge, Number of positions: 3, Color: red                                                                                                                                                 |
| 3030187             | FBS 4-5                | Plug-in bridge, Number of positions: 4, Color: red                                                                                                                                                 |
| 3030190             | FBS 5-5                | Plug-in bridge, Number of positions: 5, Color: red                                                                                                                                                 |
| 3030213             | FBS 10-5               | Plug-in bridge, Number of positions: 10, Color: red                                                                                                                                                |
| 3030226             | FBS 20-5               | Plug-in bridge, Number of positions: 20, Color: red                                                                                                                                                |
| 3038930             | FBS 50-5               | Plug-in bridge, Number of positions: 50, Color: red                                                                                                                                                |
| <b>General</b>      |                        |                                                                                                                                                                                                    |
| 3047303             | DP-UTTB 2,5/4          | Spacer plate, Length: 69.9 mm, Width: 2.6 mm, Height: 33 mm, Color: gray                                                                                                                           |
| 3047358             | FBS-PV UT              | Vertical potential bridge, to connect the upper and lower level                                                                                                                                    |
| <b>Marking</b>      |                        |                                                                                                                                                                                                    |
| 0811228             | X-PEN 0,35             | Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm                                                                            |
| 1050004             | ZB 5 :UNBEDRUCKT       | Zack strip, unprinted, 10-section, for individual labeling with M-PEN, ZB-T or CMS system, pack is sufficient for 100 terminal blocks, for a terminal width of 5.2 mm, color: White                |
| 5060906             | ZB 5/WH-100:UNBEDRUCKT | Zack strip, unprinted: 10-section, for individual labeling with M-PEN, ZB-T or CMS system, large batch, sufficient for labeling 1000 terminal blocks, for a terminal width of 5.2 mm, color: White |
| 1050295             | ZB 5:SO/CMS            | Zack strip, 10-section, divisible, special printing, marking according to customer requirements                                                                                                    |
| <b>Plug/Adapter</b> |                        |                                                                                                                                                                                                    |
| 0201689             | MPS-IH BU              | Insulating sleeve, Color: blue                                                                                                                                                                     |
| 0201676             | MPS-IH RD              | Insulating sleeve, Color: red                                                                                                                                                                      |
| 0201663             | MPS-IH WH              | Insulating sleeve, Color: white                                                                                                                                                                    |
| 0201744             | MPS-MT                 | Test plugs                                                                                                                                                                                         |
| 3030925             | PAI-4                  | Test adapter, Color: gray                                                                                                                                                                          |

|              |             |                                                                                                                                                                  |
|--------------|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 3030983      | PS-5        | Test adapter, Color: red                                                                                                                                         |
| <b>Tools</b> |             |                                                                                                                                                                  |
| 1205053      | SZS 0,6X3,5 | Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip |

**Address**

PHOENIX CONTACT Inc., USA  
586 Fulling Mill Road  
Middletown, PA 17057, USA  
Phone (800) 888-7388  
Fax (717) 944-1625  
<http://www.phoenixcon.com>



© 2011 Phoenix Contact  
Technical modifications reserved;