

# C-SD05VL

DNR Golf Ball Dome Camera with IR LED's



The C-SD05VL Golf Ball Dome Camera features a 3.4mm fixed Conic Lens, delivering sharp images with 700 TVL Resolution. The camera is housed in a metal case, with an IP rating of IP65.

The 3.4mm lens makes the camera ideal for almost any indoor or outdoor application, offering a great deal of flexibility. The camera has an incredibly wide angle view, suitable for overview type surveillance, with narrower angles being suitable for scenes such as aisles in stores. With 10 built-in IR LED's enabling a distance of upto 10M IR Illumination.

The small and discrete design allows the unit to blend in with almost any environment. This camera is ideal for covert, vehicles, & door entrance applications. The camera is so small it can actually be mounted on or beside cash registers, countertops, or shelves.

## Key features

- ▶ 1/3" Inch Colour 960H CCD
- ▶ 3.4mm Fixed Conic Lens
- ▶ High Resolution : 700TVL
- ▶ Indoor or outdoor applications
- ▶ Ingress Protection Rating: IP65
- ▶ 10 Built-in IR LED's
- ▶ Min. Illumination : 0 Lux (IR LED'S ON)
- ▶ Highest Resolution: Vivid Sharp Picture in completely darkness
- ▶ Power DC 12V

# C-SD05VL


## DNR Mini Ball Dome Camera with IR LED's

### Specifications

Description / Model	C-SD05VL
Sensor Type	1/3" Inch Color 960H CCD
Effective pixels	976 (H) X 494 (V) approx. 480K pixels (NTSC) 976 (H) X 582 (V) approx. 570K pixels (PAL)
Total pixels	1020 (H) X 508 (V) approx. 520K pixels (NTSC) 1020 (H) X 596 (V) approx. 610K pixels (PAL)
Resolution	700 TV Lines
Scanning system	2:1 Interlace
Min. illumination	0 Lux (IR LED ON)
Video Output	1.0Vp-p Composite. 75 Ohms
S/N Ratio	52dB
Power Source	DC 12V
Power Consumption	IR LED ON: 250mA Max
Lens	3.4mm Conic Lens
IR illumination	10 built-in IR LED's up to 10M range
Storage Temperature	-20° ~ +60°(Humidity : 20%RH ~ 95%RH)
Operating Temperature	-10° ~ +50°(Humidity : 20%RH ~ 80%RH)
IP Ratio	IP65
Dimension (W x H x D)	48mm(W) * 46mm(H) * 48mm(D)
Weight	100g

NB. Specification subject to change without notification

### Dimensions



### Applications

- ▶ Retail
  - ▶ Leisure Complexes
  - ▶ Supermarkets
- ▶ Office Complexes
  - ▶ Schools
  - ▶ Public Transport
- ▶ Colleges
  - ▶ Restaurants
  - ▶ Petrol stations