

## Round cable - CABLE-FCN40/4X14/ 2,0M/M340 - 2321732

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Assembled round cable (40-pos. Fujitsu strip on four 14-pos. FLK strips) for coupling 32 channels to I/O cards of MODICON® M340 (BMX DDI 3202K, BMX DDI 6402K, BMX DD0 3202K, BMX DD0 6402K, BMX DDM 3202K); cable length 2 m



### Why buy this product

- Splitting 32 channels into 4 x 8 channels

### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 412209
Weight per Piece (excluding packing)	409.2 g
Custom tariff number	85444290
Country of origin	Germany

### Technical data

#### General

Nominal voltage $U_N$	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega$ /m
Length of cable	2 m
Single wire, cross section	0.14 mm <sup>2</sup>
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	6.3 mm
Shielding	no
Outer sheath, material	PVC
External sheath, color	RAL7035

#### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Round cable - CABLE-FCN40/4X14/ 2,0M/M340 - 2321732

### Technical data

#### Environmental conditions

Flame resistance	IEC 60332-1
Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

#### Connector, module side

Number of positions	14
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	4

#### Connector, controller side

Number of positions	40
Connectors	Fujitsu connector
Number of plugs	1

#### Supported controller

Control	Schneider Electric MODICON M340
- suitable I/O card	BMX DDI 3202K
	BMX DDI 6402K
	BMX DD0 3202K
	BMX DD0 6402K
	BMX DDM 3202K

### Classifications

#### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

#### ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

#### UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620

## Round cable - CABLE-FCN40/4X14/ 2,0M/M340 - 2321732

### Classifications

#### UNSPSC

UNSPSC 12.01	26121620
UNSPSC 13.2	26121620