


WRENCH SETS



Combination Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
ND336T*#	Metric: 10, 11, 12, 13, 14, 17, 19mm	7	0.73
ND349K#	8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	12	1.23
ND360E	7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 23, 24mm	17	2.81
ND235C*#	A/F: 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 in	7	0.82
ND243L#	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16 in	10	1.84
ND251D	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1, 1 1/16, 1 1/8, 1 1/4 in	14	4.42
ND130A	Whitworth: 1/8, 3/16, 1/4, 5/16, 3/8, 7/16, 1/2 W	7	1.18
ND150J	1/8, 3/16, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 W	11	4.13

Mini Combination Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
SRJSM14	Metric: 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	14	0.86
SRJS11	A/F: 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 in	11	0.60

Open Jaw Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
NB331T*	Metric: 6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19mm	7	0.57
NB351G	6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 20 x 22, 21 x 23, 24 x 26, 27 x 30mm	11	1.90
NB227D*	A/F: 5/16 x 3/8, 7/16 x 1/2, 9/16 x 5/8, 11/16 x 3/4, 13/16 x 7/8, 15/16 x 1 in	6	0.90
NB231E*	5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 1/2 x 9/16, 9/16 x 5/8, 5/8 x 11/16, 11/16 x 3/4 in	7	0.64
NB250P	1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 1/2 x 9/16, 9/16 x 5/8, 5/8 x 11/16, 11/16 x 3/4, 3/4 x 7/8, 15/16 x 1 in	10	1.22
NB131R	Whitworth: 1/8 x 3/16, 3/16 x 1/4, 1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 1/2 x 9/16 W	7	1.08
NB141C	1/8 x 3/16, 3/16 x 1/4, 1/4 x 5/16, 5/16 x 3/8, 3/8 x 7/16, 7/16 x 1/2, 1/2 x 9/16, 9/16 x 5/8, 5/8 x 11/16 W	9	1.96

Midget Open Jaw Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
NB310F*	Metric: 3.2 x 4, 4 x 5, 5 x 5.5, 5.5 x 7, 6 x 7, 7 x 8mm	6	0.08
NB209E*	A/F: 3/16 x 1/4, 1/4 x 5/16, 5/16 x 11/32, 5/16 x 3/8, 3/8 x 7/16 in	5	0.08
NB108T*	BA: 11 x 9, 10 x 8, 7 x 5, 6 x 4, 3 x 1, 2 x 0	6	0.12

Ring Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
NC381T	Metric: 6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19 mm	7	0.77
NC389N	6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 21 x 23, 22 x 24, 24 x 27mm	10	2.17
NC278P	A/F: 1/4 x 5/16, 3/8 x 7/16, 1/2 x 9/16, 5/8 x 11/16, 3/4 x 7/8, 15/16 x 1 in	6	1.09
NC181R	Whitworth: 1/8 x 3/16, 1/4 x 5/16, 3/8 x 7/16, 1/2 x 9/16, 11/16 x 3/4 W	5	1.78

Mini Ring Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
NC328R	8 x 9, 10 x 11, 12 x 13, 14 x 15, 17 x 19 mm	5	0.28

Crescent Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
SCWB6	7/16 x 1/2, 9/16 x 5/8 in, 10 x 12, 11 x 13, 14 x 17, 15 x 19 mm	6	0.58

Flare Crow Foot Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
SACFM10	10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	10	0.47
SACF7	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 in	7	0.33

Open Jaw Crow Foot Wrenches

Ref.	Sizes	Pieces per set	Wt. kg
SACJM10	10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm	10	0.36
SACJ7	3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4 in	7	0.25

Wrench sets marked * are supplied in red PVC wallets.
Wrench sets marked # can be supplied in blue canvas wallets, to order use Ref. plus BW (ie ND336TBW).