

# SIEMENS

## Product data sheet


**3SB3403-0C**


CONTACT BLOCK,  
WITH ONE CONTACT ELEMENT, 1NC,  
1-POLE WITH CAGE CLAMP CONNECTION

### General technical details:

|  |                  |
|--|------------------|
| Product designation                                  | switching magnet |
| Operating current / at AC-15 / at 230 V              |                  |
| • at 50 Hz / rated value                             | 6 A              |
| • at 60 Hz / rated value                             | 6 A              |
| Operating current / at DC-13 / at 24 V / rated value | 3 A              |
| Type of voltage                                      |                  |
| • of the operating voltage                           | AC/DC            |
| Operating voltage                                    |                  |
| • for DC / rated value / maximum                     | 230 V            |
| • for DC / rated value / minimum                     | 5 V              |
| • 1 / for DC   | 24 V             |
| • 1 / at 50 Hz / for AC / rated value                | 400 V            |
| • 1 / at 60 Hz / for AC / rated value                | 300 V            |
| • at 50 Hz / for AC / rated value / minimum          | 5 V              |
| • at 50 Hz / for AC / rated value / maximum          | 400 V            |
| • at 60 Hz / for AC / rated value / minimum          | 5 V              |
| • at 60 Hz / for AC / rated value / maximum          | 300 V            |
| Number of NC contacts / for auxiliary contact        | 1                |

|  |                         |
|--|-------------------------|
| Number of NO contacts / for auxiliary contact          | 0                       |
| Number of change-over switches / for auxiliary contact | 0                       |
| Suitability for integration                            | front element           |
| • Suspension button                                    | Yes                     |
| • Pressure selection button                            | Yes                     |
| • Front element  | Yes                     |
| • Suspension button                                    | Yes                     |
| <b>Mechanical design:</b>                              |                         |
| Design of the electrical connection                    | spring-loaded terminals |
| Type of fixing/fixation                                | front mounting          |
| <b>Ambient conditions:</b>                             |                         |
| Protection class IP                                    | IP20                    |



**last change:**

10/31/2006

|                              |  |
|------------------------------|--|
| <b>Technical Assistance:</b> | Telephone: +49 (0) 911-895-5900 (8 <sup>00</sup> - 17 <sup>00</sup> CET)   |
|                              | Fax: +49 (0) 911-895-5907  |
|                              | E-Mail: <a href="mailto:technical-assistance@siemens.com">technical-assistance@siemens.com</a>                               |
|                              | Internet: <a href="http://www.siemens.de/lowvoltage/technical-assistance">www.siemens.de/lowvoltage/technical-assistance</a> |