

## Crimping pliers - CRIMPFOX-C120 - 1212318

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Basic pliers, for accommodating dies for a wide range of contact types up to 120 mm<sup>2</sup>

### Why buy this product

- ✓ Wide variety of available dies
- ✓ A mechanical drive system keeps the level of force required to an absolute minimum
- ✓ Easily foldable jaw holders mean that the dies can be changed quickly



### Key commercial data

Packing unit	1 pc
GTIN	 4 046356 454643
Weight per Piece (excluding packing)	2489.9 g
Custom tariff number	82055980
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	430 mm
Height	65 mm
Width (a)	130 mm

#### General

Color	black
Compression	universal

### Classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301

# Crimping pliers - CRIMPFOX-C120 - 1212318

## Classifications

### eCl@ss

eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Accessories

Accessories

Die

## Crimping pliers - CRIMPFOX-C120 - 1212318

### Accessories

Replacement die - CRIMPFOX-C120 AI 70/M-DIE - 1212335



Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 70 mm<sup>2</sup>, trapeze crimp

---

Replacement die - CRIMPFOX-C120 AI 95/M-DIE - 1212336



Die (upper part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm<sup>2</sup>, trapeze crimp

---

Replacement die - CRIMPFOX-C120 AI 50/F-DIE - 1212337



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 50 mm<sup>2</sup>, trapeze crimp

---

Replacement die - CRIMPFOX-C120 AI 70/F-DIE - 1212338



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 70 mm<sup>2</sup>, trapeze crimp

---

Replacement die - CRIMPFOX-C120 AI 95/F-DIE - 1212339



Die (lower part), for CRIMPFOX-C120, for ferrules (DIN 46228) 95 mm<sup>2</sup>, trapeze crimp

---

## Crimping pliers - CRIMPFOX-C120 - 1212318

### Accessories

Replacement die - CRIMPFOX-C120 RCI 10/DIE - 1212327



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 10 mm<sup>2</sup>, oval crimp

---

Replacement die - CRIMPFOX-C120 RCI 16/DIE - 1212328



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 16 mm<sup>2</sup>, oval crimp

---

Replacement die - CRIMPFOX-C120 RCI 25/DIE - 1212329



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 25 mm<sup>2</sup>, oval crimp

---

Replacement die - CRIMPFOX-C120 RCI 35/DIE - 1212330



Die (pair), for CRIMPFOX-C120, for insulated ring cable lug 35 mm<sup>2</sup>, oval crimp

---

Replacement die - CRIMPFOX-C120 RC 70/M-DIE - 1212331



Die (upper part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 6 + 70 mm<sup>2</sup>, indent crimp

---

## Crimping pliers - CRIMPFOX-C120 - 1212318

### Accessories

Replacement die - CRIMPFOX-C120 RC 35/F-DIE - 1212332



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 10 + 16 + 25 + 35 mm<sup>2</sup>, indent crimp

---

Replacement die - CRIMPFOX-C120 RC 50/F-DIE - 1212333



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 6 + 50 mm<sup>2</sup>, indent crimp

---

Replacement die - CRIMPFOX-C120 RC 70/F-DIE - 1212334



Die (lower part), for CRIMPFOX-C120, for non-insulated cable lugs (DIN 46234) 10 + 70 mm<sup>2</sup>, indent crimp

---

Replacement die - CRIMPFOX-C120 RCT 35-1/DIE - 1212320



Die (pair), for CRIMPFOX-C120, for copper tube lug 16 + 35 mm<sup>2</sup>, WM crimp

---

Replacement die - CRIMPFOX-C120 RCT 50-1/DIE - 1212321



Die (pair), for CRIMPFOX-C120, for copper tube lug 25 + 50 mm<sup>2</sup>, WM crimp

---

## Crimping pliers - CRIMPFOX-C120 - 1212318

### Accessories

Replacement die - CRIMPFOX-C120 RCT 70-1/DIE - 1212319



Die (pair), for CRIMPFOX-C120, for copper tube lug 10 + 70 mm<sup>2</sup>, WM crimp

---

Replacement die - CRIMPFOX-C120 RCT 95-1/DIE - 1212322



Die (pair), for CRIMPFOX-C120, for copper tube lug 95 mm<sup>2</sup>, WM crimp

---

Replacement die - CRIMPFOX-C120 RCT 120-1/DIE - 1212323



Die (pair), for CRIMPFOX-C120, for copper tube lug 120 mm<sup>2</sup>, WM crimp

---

Replacement die - CRIMPFOX-C120 R25-50/DIE - 1212324



pre-round die (pair), for CRIMPFOX-C120, for sector cable 25 + 50 mm<sup>2</sup>

---

Replacement die - CRIMPFOX-C120 R35-70/DIE - 1212325



pre-round die (pair), for CRIMPFOX-C120, for sector cable 35 + 70 mm<sup>2</sup>

---

## Crimping pliers - CRIMPFOX-C120 - 1212318

### Accessories

Replacement die - CRIMPFOX-C120 R95/DIE - 1212326



Pre-round die (pair), for CRIMPFOX-C120, for sector cable 95 mm<sup>2</sup>