

## Mini-Lynx GLS

ML GLS 827 E27 15W SLV

0035505

### Range features



CE

### PRODUCT OVERVIEW

Ordering number	0035505
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	10000
Lamp shape	GLS
Lamp finish	Frosted
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355054
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	820
Efficacy (Rated) (lm/w)	55
Watt (Nominal) (W)	15
Equivalent watt (W)	65
Voltage (V)	220-240

# Mini-Lynx GLS

ML GLS 827 E27 15W SLV

**0035505**

## DATA TABLE

### General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035505
Energy saving lamp	Yes
Average life (Rated) (h)	10000
Energy class	A
Average life (Nominal) (h)	10000
Lamp finish	Frosted
Lamp shape	GLS
Dimmable	No
Cap/Base	E27
Type	GLS
EAN code	5410288355054
E-number FI	4940415
E-number SE	8357584

### Long description

Product name	ML GLS 827 E27 15W SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.0
Warm-up time to 60% of full light (max) (s)	<100
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

### Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	820
Lumen maintenance at end of nominal life (%)	60
Luminous flux (Nominal) (lm)	820

## Mini-Lynx GLS

*ML GLS 827 E27 15W SLV*

**0035505**

### Electrical data

<b>kWh per 1000 hours burning time</b>	15
<b>Efficacy (Rated) (lm/w)</b>	55
<b>Watt (Rated) (W)</b>	15
<b>Watt (Nominal) (W)</b>	15
<b>Equivalent watt (W)</b>	65
<b>Voltage (V)</b>	220-240
<b>Lamp power factor</b>	=0.55

### Physical data

<b>Weight (kg)</b>	0.08
<b>Lamp Length (mm) - C/L</b>	130±2
<b>Max. Lamp Diameter (mm) - D</b>	64±1
<b>Single packaging type</b>	Box/Sleeve
<b>Single package dimensions (L x W x H) (cm)</b>	14.50 x 7.00 x 7.00
<b>Outer package dimensions (L x W x H) (cm)</b>	36.00 x 15.50 x 17.00


## Mini-Lynx GLS

ML GLS 827 E27 15W SLV

0035505

### TECHNICAL DRAWINGS

---



### ENERGY LABEL

---

