



iM2435

Medium Case

Travel Case



Meets airline regulations for carry-on luggage*

- **Meets airline regulations for carry-on**

luggage* Lightweight Strong HPX® Resin

- Lightweight Strong HPX® Resin Watertight, crushproof and dustproof

- Watertight, crushproof and dustproof O-ring seal

- O-ring seal In-line Wheels

- In-line Wheels Two Press & Pull Latches

- Two Press & Pull Latches Two stainless steel padlock protectors

- Two stainless steel padlock protectors 38" (96.5cm)

Retractable Extension Handle

- 38" (96.5cm) Retractable Extension Handle *Check with your airline for exact measurement requirements

- *Check with your airline for exact measurement requirements Peli's limited lifetime guarantee**

- Peli's limited lifetime guarantee****Where applicable by law

- **Where applicable by law

CONFIGURATIONS

iM2435 - Standard

iM2435-X0000 - With No Foam

iM2435-X0002 - With With Padded Dividers & Lid Organizer

DIMENSIONS

Interior (L x W x D): 17.50 x 6.50" x 15.50 (44.5 x 16.5 x 39.4 cm)

Exterior (L x W x D): 18.63 x 9.25" x 16.50 (47.3 x 23.5 x 41.9 cm)

Lid Depth: 2.00"

Bottom Depth: 13.50"

Total Depth: 15.5"

Int Volume: 1.02 ft³

MATERIALS

Body: Injection Molded HPX® high performance resin

Latch: Valox - Polybutylene Terephthalate (PBT)

Latch (Alt): Xenoy - Polyester/Polycarbonate blend

O-Ring: Silicone Sponge

Pins: Stainless Steel

Pins (Alt): Aluminum

Foam: 1.3/1.35 polyester

Purge Body: Valox - Polybutylene Terephthalate (PBT)

Purge Body (Alt): Xenoy - Polyester/Polycarbonate blend

Purge Vent: Gortex membrane

Purge O-Ring: Buna-N, 50-60 Durometer Shore A

COLOURS



Black



OD Green

WEIGHT

Weight With Foam: 11.15 lbs

Weight Without Foam: 10.00 lbs

Buoyancy: 56.70 lbs

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

FOAM PROPERTIES

Layer 1 (Lid): 2.00" Convolute

Layer 2 (Base): 2.13" Pick N Pluck

Layer 3 (Base): 2.31" Pick N Pluck

Layer 4 (Base): 2.31" Pick N Pluck

Layer 5 (Base): 1.88" Pick N Pluck

Layer 6 (Base): 0.50" Pad

OTHER

Extendable Handle: yes

Master Pack: 1

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com