


Positive Lock Connection System

Straight Receptacles Mark I 6.3 mm (.250 Series)

Tab Thickness - 0.8 mm



Wire Range (mm ²)	Insulation Diameter (mm)	Material and Finish	Part Number	
			Strip Form	Loose Piece
0.5-1.0	2.0-3.3	Ph. Bronze	927867-2	-
		Brass-Tin Plated	927867-6	-
		Ph. Bronze-Tin Plated	927867-7	-
0.5-1.0	1.4-2.3	Brass	927852-1	-
		Ph. Bronze	927852-2	-
		Brass-Tin Plated	927852-6	-
		Ph. Bronze-Tin Plated	927852-7	-
		Ph. Bronze-Tin Plated	927852-8	-
0.5-1.5	2.3-3.3	Brass	160759-1	160773-1
		Ph. Bronze	160759-2	-
		Brass-Tin Plated	160759-3	160773-3
		Ph. Bronze-Tin Plated	160759-4	160773-4
		Brass	281827-1 ¹	-
		Brass-Tin Plated	281827-2 ¹	-
		Brass-Tin Plated	1-160759-1	-
0.7-2.0	2.4-3.2	Ph. Bronze-Tin Plated	1-160759-2	160773-7
		Brass	154718-1	341002-1
		Ph. Bronze	154718-2	-
		Ph. Bronze-Tin Plated	154718-4	-
		Brass-Tin Plated	154718-6	341002-6
1.0-2.5	3.0-4.3	Ph. Bronze-Tin Plated	154718-7	-
		Brass	160831-1	928901-1
		Ph. Bronze	160831-2	928901-2
		Brass-Tin Plated	160831-3	928901-3
1.0-2.5	2.7-4.0	Ph. Bronze-Tin Plated	160831-4	928901-4
		Ph. Bronze	927881-2	-
1.0-2.5	2.1-3.1	Ph. Bronze-Silver Plated	927881-8	927882-8
		Brass	927854-1	927855-1
		Ph. Bronze	927854-2	927855-2
		Brass-Tin Plated	927854-6	927855-6
		Ph. Bronze-Tin Plated	927854-7	927855-7
2.5-4.0	3.6-4.3	Ph. Bronze-Silver Plated	927854-8	927855-8
		Brass	154717-1	341001-1
		Ph. Bronze	154717-2	341001-2
		Brass-Tin Plated	154717-3	321001-3
		Ph. Bronze-Tin Plated	154717-4	-
		Brass-Tin Plated	154717-6	-
		Ph. Bronze-Tin Plated	154717-7	-
		Ph. Bronze-Silver Plated	154717-8	-
2.5-4.0	3.3-4.7	Brass-Tin Plated	281828-2 ¹	-
		Ph. Bronze	928958-2	-
		Brass-Tin Plated	928958-6	928959-6
		Ph. Bronze-Tin Plated	928958-7	-
		Ph. Bronze-Silver Plated	928958-8	928959-8
4.0-6.0	4.0-5.3	Brass	928960-1	-
		Ph. Bronze	928960-2	-
		Brass-Tin Plated	928960-6	928961-6
		Ph. Bronze-Tin Plated	928960-7	928961-7
		Ph. Bronze-Silver Plated	928960-8	928961-8
4.0-6.0	3.4-5.1	Brass-Tin Plated	790319-2	737015-2
		Brass-Tin Plated	790319-3	737015-3
		Ph. Bronze	790319-4	737015-4
		Brass-Tin Plated	281829-2 ¹	-

¹ With anti-overstress latching