



GREASE GUN



PART NO.	CAPACITY			G.W. (kg)
97201	100cc	6	24	20.0

- 3 way multi-load grease gun with pipe and coupler
- Cartridge, bulk, or dispenser filling
- Cast iron pump head with steel precision plunger prevents by-passing of lubricants
- Positive lock for easy filling and safe operation
- Up to 4,500 psi maximum pressure

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



GREASE GUN



PART NO.	CAPACITY			G.W. (kg)
97202	400cc	6	12	18.0

- 3 way multi-load grease gun with pipe and coupler
- Cartridge, bulk, or dispenser filling
- Cast iron pump head with steel precision plunger prevents by-passing of lubricants
- Builds up to 10,000 psi maximum pressure
- Unique removeable the end cap for easy filling

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



GREASE GUN



PART NO.	CAPACITY			G.W. (kg)
97203	400cc	6	12	18.0

- 3 way multi-load grease gun with pipe and coupler
- Cartridge, bulk, or dispenser filling
- Cast iron pump head with steel precision plunger prevents by-passing of lubricants
- Builds up to 10,000 psi maximum pressure
- Unique removeable the end cap for easy filling

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



GREASE COUPLER



PART NO.			G.W. (kg)
97211	12	28.8	20.3

- Works with hydraulic-type grease fittings

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



HIGH PRESSURE FLEXIBLE NYLON HOSE

PART NO.	SIZE MM			G.W. (kg)
97212	300	12	288	25.0
97213	450	12	192	25.0



- Heavy-duty flexible nylon hose
- Strategically placed coil spring provides non-slip, push-pull grip and prevents accidental "Kinking" which could cause hose ruptures

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



AIR BLOW GUNS

New

PART NO.	SIZE MM			G.W. (kg)
97221	100	30	60	13.0
97222	250		30	14.0



- 3 way multi-load grease gun with pipe and coupler
- Cartridge, bulk, or dispenser filling
- Cast iron pump head with steel precision plunger prevents by-passing of lubricants
- Builds up to 10,000 psi maximum pressure
- Unique removeable the end cap for easy filling

⚠ Nature of this product is subject to wear and tear upon usage. Not covered under Lifetime Warranty.



TUBING FLARING TOOL SET



New

PART NO.			G.W. (kg)
97321	6	36	17.5

- Flares o.d. tubing
- Hole size: 3/16", 1/4", 5/16", 3/8", 7/16", 1/2", 5/8"
- Machined grooves for fit Sliding T-handle





3/8" DR. END CAP OIL FILTER WRENCH

PART NO.	SIZE MM			G.W. (kg)
97401	65	4	32	6.0
97403	74/76	4	32	6.4
97404	76	4	32	6.4
97405	80	4	32	6.8
97406	90	4	32	6.8
97407	93	4	32	6.8

- 97401 - Fits on Toyota, Nissan, Changan Alto, Lexus, Diahatsu.
- 97403 - Fits on Buick, GM, Saturn.
- 97404 - Fits on Mopar, VW, Porsche, Mercedes, BMW...
- 97405 - Fits on Honda Accord, Nissan, Toyota...
- 97406 - Fits on Honda Accord, Mitsubishi, Mopar, Isuzu...
- 97407 - Fits on GM, Fram, Hastings, Purolator, WIX, Nissan, VW,



TWO WAY OIL FILTER WRENCH



PART NO.	SIZE MM			G.W. (kg)
97422	63-102	2	16	7.4

- Two-way action installs or removes filters
- Works with 1/2" and 3/8" drive tools



OIL FILTER WRENCH

New

PART NO.	SIZE INCH			G.W. (kg)
97426	12"	6	36	17.5

