

ESD 2300 SERVICE SET

Special tool set for repair and maintenance of electrostatically endangered components



2300 **BERNSTEIN** ESD Service set with tools

Description:

The foldable green portfolio at the same time serves as an electrically **conductive** workbench pad of 680 x 680 x 0.35 mm. The surface resistance according to DIN 53482 is approx. 10^9 ohm.

The workbench pad has 3 press-stud receptacles for connecting the contact bracelet and the earth wire. With 2 additional press-buttons the pad may be closed as a tool bag.

The 2 patch pockets carry the contact bracelet and the earth wire. Furthermore 16 conductive tools are placed in pockets, ready to hand.

Outside dimensions: 330 x 240 x 20 mm (when closed)

Weight with tools: approx. 0.850 kg

Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-166	Glass fibre contact cleaner , with rotary mechanism, plastic casing	5-191	Tweezers , 120 mm, made from conductive, black plastic material, reinforced with glass fibre, with rounded tips
2-620	PLCC-extractor	5-194	Tweezers , 120 mm, made from conductive, black plastic material, reinforced with glass fibre, with bent, pointed tips
3-601-13	Side cutters , 120 mm, for hard wire up to 0.4 mm Ø, for soft wire up to 1.0 mm Ø, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard	6-616	Socket wrench with conductive handle, blade made from chrome vanadium, nickel-plated, A/F 3.5 mm
3-633-13	Snipe nose pliers , 120 mm, bright steel-polished, box joint, double leaf spring, with conductive black hand-guard	6-661	TORX screwdriver T 5 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
4-601	Screwdriver 50 x 0.8 mm , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip	6-664 L	TORX screwdriver T 8 , with bore-hole in the tip, with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
4-605	Screwdriver 60 x 2.0 mm , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip	6-666 L	TORX screwdriver T 10 , with bore-hole in the tip, with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
4-606	Screwdriver 60 x 2.5 mm , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip	9-342	Contact bracelet cloth armband, allergy-free, edges and surface insulating, spiral cord, 1 Mohm safety resistor, combined press-stud and terminal connection, to DIN EN 100 015/1
4-621	Cross-recess screwdriver size 000 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip	9-346	Earth wire with 1 Mohm safety resistor, 2500 mm long, with terminal connection resp. press-stud, for connecting workbench pad and floor cover and connection to an earth potential
4-622	Cross-recess screwdriver size 00 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip		
4-623	Cross-recess screwdriver size 0 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip		