



QQGQ8.E173199
Power Supplies, Information Technology Equipment Including Electrical Business
Equipment Certified for Canada - Component

[Page Bottom](#)

Power Supplies, Information Technology Equipment Including Electrical Business
Equipment Certified for Canada - Component

[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment Certified for Canada - Component](#)

MASCOT ELECTRONICS AS
 MOSSEVEIEN 109
 PO BOX 177
 N-1601 FREDRIKSTAD, NORWAY

E173199

Model No.	Rated Input		SC	Max Output			OC	SP	EP	FC	GC
	Volts	Hz		V	A	VA					
"2241 Series".											
Switch Mode Power Supply / Battery Charger											
	100-240ac	50-60	2	16.8dc	0.9	14	3	60950-1	20	-	-
2099	100-240ac	50/60	0	17.18	3.48	48.7	3	950	20B	0	1
				7.26	4.77	23	3				
				3.31	11.25	26.66	3				
				390	0.39	150	4				
2515 series (Mascot branded)											
	10-30dc	-	3	-	2.2	-	3	60950-1	n/a	5	-
9925	100-250ac	50-60	0	9.3	0.65	6.05	3	1950	20B	0	0
9990	100-250ac	50/60	0	12.2	4.2	43.1	3	950	-	0	0
				5.1	4.6	19.4	3				
				4.1	9.2	15.1	3				
9992	100-240ac	50-60	0	12.1	1.15	14.4	3	950	20B	0	1
				5.1	2.08	10	3				
				3.4	4.83	15	3				
				390	0.38	150	4				
9995+9996											
	100-250ac	50/60	0	17.9	5.6	37.1	3	950	-	0	0
				6.5	3.6	11.7	3				
				3.3	8.6	17	3				
9999	100-240ac	50/60	0	17.18	3.48	48.7	3	950	20B	0	1
				7.26	4.77	23	3				
				3.31	11.25	26.66	3				
				390	0.39	150	4				
DAS771457AA (e2v branded)											
	10-30dc	-	3	-	1.0	-	3	60950-1	n/a	5	-
SEE60-08TE-12V											

	100-240ac	50/60	0	14	7.5	70	3	950	-	0	0
SEE60-08TE-15V											
	100-240ac	50/60	0	17.5	7	84.2	3	950	-	0	0
SEE60-08TE-24V											
	100-240ac	50/60	0	28	4.5	77	3	950	-	0	0
SEE60-08TE-5V											
	100-240ac	50/60	0	6	17	71.5	3	950	-	0	0



Marking: Company name, model designation and Recognized Component Mark for Canada, .

Last Updated on 2011-12-06

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

© 2012 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2012 UL LLC".