

LEDLENSER i9R-iron

The Ledlenser i9R-iron is a rechargeable industrial hand torch that can be charged in just two hours, thanks to its ultra-fast Safety Ytrion Cell battery. This makes it ideal for industrial users like engineers, inspectors and craftsmen, looking for a fully-powered torch in a hurry. Tough and well-made as is to be expected from any Ledlenser, it has a large metal body that holds a CREE® Power+ LED Light Chip, which can deliver up to 400 lumens of precise white light some 260 metres into the distance. Light quality is astounding because it features Ledlenser's patented Advance Focus System to maintain homogenous, consistent light at all times. There is a choice of Power or Low Power light settings, providing everything from high-intensity illumination down to a softer light useful for reading maps or viewing diagrams. A single-handed Speed Focus with Fast Lock prevents the i9 from refocusing by accident, and a roll protection ring helps prevent it from dropping off a work surface. Diamond knurling on the barrel provides safe grip for sweaty or oily hands, while a robust metal body and internal gold-plated battery contacts offer the kind of uncompromising strength that sets the i9R-iron apart as an essential tool for any site or workshop.

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Larger-bodied rechargeable industrial hand torch
- CREE® Power+ LED Light Chip
- State-of-the-art, reliable German engineering
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Speed Focus® with Fast Lock
- Dynamic Switch
- Power and Low Power light modes
- Charging base with UK plug adaptor and charging light indicator
- Ultra-fast 2 hour charging via Safety Ytrion Cell
- Water-resistant (IPX4)
- Robust metal housing.
- Detachable roll protection ring included
- Supplied with: Docking/Charging Station, UK Power Plug, Roll Protection Ring, Pouch, Wrist-strap, Rechargeable battery set (1 x Li-iron)

Technical Information

i9R iron	BOOST	POWER	LOW POWER
POWER	x	400 lumens	40 lumens
BEAM DISTANCE	x	260 metres	80 metres
RUN TIME	x	6 hours	35 hours
SIZE	158x39mm	WEIGHT	260g

Supplied with: Docking/Charging Station, Power Plug, USB Cable, Roll Protection Ring, Pouch, Wrist-strap, Rechargeable battery set (1 x Li-iron)



Code	Description	Unit Colour	Packaging	Barcode
5609Ri	i9Ri	Black	Box	4029113560962

RRP ex.vat £104.12 / incl.vat £124.95