

Product Selection

Single Connector Cables

Micro-Style
Straight Female

Micro-Style Straight Female

Voltage Style	Number of Pins	Gauge	Length	Pin Configuration/Wire Colors (Face View Female Shown)	PVC Jacket Catalog Number	PUR Jacket Catalog Number
Standard Cables						
AC	3-pin, 3-wire	18 AWG	6.0 ft (2m)	1-Green 2-Red/Black 3-Red/White	CSAS3F3CY1802	—
			16.4 ft (5m)		CSAS3F3CY1805	—
			32.8 ft (10m)		CSAS3F3CY1810	—
		22 AWG	6.0 ft (2m)		CSAS3F3CY2202	CSAS3F3RY2202
			16.4 ft (5m)		CSAS3F3CY2205	CSAS3F3RY2205
			32.8 ft (10m)		CSAS3F3CY2210	CSAS3F3RY2210
	4-pin, 4-wire	18 AWG	6.0 ft (2m)	1-Red/Black 2-Red/White 3-Red 4-Green	CSAS4F4CY1802	—
			16.4 ft (5m)		CSAS4F4CY1805	—
			32.8 ft (10m)		CSAS4F4CY1810	—
		22 AWG	6.0 ft (2m)		CSAS4F4CY2202	CSAS4F4RY2202
			16.4 ft (5m)		CSAS4F4CY2205	CSAS4F4RY2205
			32.8 ft (10m)		CSAS4F4CY2210	CSAS4F4RY2210
	22 AWG	22 AWG	6.0 ft (2m)	1-Brown 2-Blue 3-Black 4-White	CSAS4A4CY2202	—
			16.4 ft (5m)		CSAS4A4CY2205	—
			32.8 ft (10m)		CSAS4A4CY2210	—
DC	5-pin, 5-wire	22 AWG	6.0 ft (2m)	1-Brown 2-Blue 3-Gray 4-Black 5-White	CSAS5A5CY2202	—
			16.4 ft (5m)		CSAS5A5CY2205	—
			32.8 ft (10m)		CSAS5A5CY2210	—
	4-pin, 3-wire	22 AWG	6.0 ft (2m)	1-Brown 2-No Wire 3-Blue 4-Black	CSDS4A3CY2202	CSDS4A3RY2202
			16.4 ft (5m)		CSDS4A3CY2205	CSDS4A3RY2205
			32.8 ft (10m)		CSDS4A3CY2210	CSDS4A3RY2210
	4-pin, 4-wire	22 AWG	6.0 ft (2m)	1-Brown 2-White 3-Blue 4-Black	CSDS4A4CY2202	CSDS4A4RY2202
			16.4 ft (5m)		CSDS4A4CY2205	CSDS4A4RY2205
			32.8 ft (10m)		CSDS4A4CY2210	CSDS4A4RY2210
	5-pin, 5-wire	22 AWG	6.0 ft (2m)	1-Brown 2-White 3-Blue 4-Black 5-Green/Yellow	CSDS5A5CY2202	—
			16.4 ft (5m)		CSDS5A5CY2205	—
			32.8 ft (10m)		CSDS5A5CY2210	—
	8-pin, 8-wire	24 AWG	16.4 ft (5m)	1-White 5-Gray 2-Brown 6-Pink 3-Green 7-Blue 4-Yellow 8-Red	CSDS8A8CB2405	—
			32.8 ft (10m)		CSDS8A8CB2410	—