

## Elite mirror light (with pull cord)

ELITE CHROME 11W LYNX-S PULL CORD

0053407



### Product features

- Slim profile 11w compact fluorescent mirrorlight for either vertical or horizontal surface mounting which is suitable for Zone 3 bathroom applications (no waterjets). Luminaire comes complete with pull cord for switching of the lamp and 11w Lynx-S warm white (2700K) lamp. Chrome finish.



## PRODUCT OVERVIEW

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	2700
<b>Colour</b>	Chrome
<b>Control gear mounting</b>	Integral
<b>Control gear type</b>	Conventional
<b>Product EAN number</b>	5410288534077
<b>Electrical protection</b>	Class II
<b>Environment</b>	Internal
<b>General application</b>	Hospitality, Residential & Consumer
<b>IP rating</b>	IP21
<b>Product code</b>	0053407
<b>Light colour</b>	Warm white
<b>Mount</b>	Wall Surface
<b>Product name</b>	ELITE CHROME 11W LYNX-S PULL CORD
<b>Included lamp</b>	0025883
<b>ETIM Class</b>	EC002892

## DATA TABLE

### General data

<b>Certifications</b>	CE
<b>Environment</b>	Internal
<b>General application</b>	Hospitality, Residential & Consumer
<b>Product code</b>	0053407
<b>Mount</b>	Wall Surface
<b>Product name</b>	ELITE CHROME 11W LYNX-S PULL CORD
<b>ETIM Class</b>	EC002892

### Optical data

<b>Colour temperature (K)</b>	2700
<b>Distribution type</b>	Symmetric

## Elite mirror light (with pull cord)

ELITE CHROME 11W LYNX-S PULL CORD

**0053407**

<b>Light colour</b>	Warm white
<b>Adjustable chromaticity</b>	N

### Electrical data

<b>Control gear mounting</b>	Integral
<b>Control gear type</b>	Conventional
<b>Electrical protection</b>	Class II
<b>Energy efficiency level</b>	A
<b>kWh per 1000 hours burning time</b>	14
<b>Mains voltage (V)</b>	100-240V~


### Physical data

<b>Colour</b>	Chrome
<b>Diffuser finish</b>	Opal
<b>Nominal Product Height (mm)</b>	92
<b>IP rating</b>	IP21
<b>Nominal Product Length (mm)</b>	480
<b>Weight (kg)</b>	0.834
<b>Nominal Product Width (mm)</b>	50

### Packaging

<b>Product EAN number</b>	5410288534077
<b>Packaging single height (cm)</b>	53.0
<b>Packaging single length (cm)</b>	5.4
<b>Single packaging type</b>	Carton
<b>Packaging single width (cm)</b>	12.0
<b>Units per outer package</b>	1
<b>Packaging outer height (cm)</b>	5.4
<b>Packaging outer length (cm)</b>	53.0
<b>Packaging outer width (cm)</b>	12.0

## TECHNICAL DRAWINGS





## Elite mirror light (with pull cord)

ELITE CHROME 11W LYNX-S PULL CORD


0053407


**SYLVANIA** 0053407

 This luminaire is compatible with bulbs of the energy classes:





This luminaire is sold with a bulb of the energy class:

874/2012 

 This luminaire is compatible with bulbs of the energy classes:

This luminaire is sold with a bulb of the energy class:



**SYLVANIA** 0053407  874/2012