

Fuse plug - P-FU 5X20 LED 250-5 - 3209264

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Fuse plug with LED for 110 - 250 V AC/DC, 0.40 - 0.95 mA, width 5.2 mm, color black




Why buy this product

- Large-surface labeling option
- Test contacts on both sides of the fuse
- Versions with bipolar defect indicator
- Can be used for overload/short-circuit protection



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 548366
Weight per Piece (excluding packing)	5.29 g
Custom tariff number	85369085
Country of origin	China

Technical data

General

Note	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

Dimensions

Width	5.2 mm
Length	23.5 mm

General

Fuse	G / 5 x 20
------	------------

Fuse plug - P-FU 5X20 LED 250-5 - 3209264

Technical data

General

Nominal current I_N	0.95 mA
Nominal voltage U_N	250 V (if used as disconnect terminal block. With fuse, the voltage is determined by the light indicator used.)
	250 V (if used as fuse terminal block)

Classifications

eCl@ss

eCl@ss 4.0	27142001
eCl@ss 4.1	27142001
eCl@ss 5.0	27142001
eCl@ss 5.1	27142001
eCl@ss 6.0	27141149
eCl@ss 7.0	27141149
eCl@ss 8.0	27141149

ETIM

ETIM 4.0	EC002018
ETIM 5.0	EC002018

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / CSA / cULus Recognized


Ex Approvals


Approvals submitted


Approval details

Fuse plug - P-FU 5X20 LED 250-5 - 3209264

Approvals

UL Recognized 	
Nominal current I _N	10 A
Nominal voltage U _N	250 V

cUL Recognized 	
Nominal current I _N	10 A
Nominal voltage U _N	250 V


CSA 	
Nominal current I _N	10 A
Nominal voltage U _N	250 V

cULus Recognized 	
--	--


Drawings

Fuse plug - P-FU 5X20 LED 250-5 - 3209264

Application drawing




Application drawing



Fuse terminal blocks in interconnected arrangement, block consisting of 5 fuse terminal blocks

Fuse plug - P-FU 5X20 LED 250-5 - 3209264

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks