



- ▶ Overclocking MEMORY
 - aXeRam
- ▶ MEMORY (for Desktop)
 - DDR3
 - DDR2
 - DDR
 - SDRAM
 - RAMBUS
- ▶ MEMORY (for Laptop)
 - DDR3
 - DDR2
 - DDR
 - SDRAM
- ▶ MEMORY (for Brands)
 - Proprietary Memory
 - Desktop Memory (Brands)
 - Laptop Memory (Brands)
 - Printer Memory
 - Server Memory
 - Workstation Memory
 - Router Memory
- ▶ FLASH CARDS
 - (CF) Compact Flash
 - (SD) Secure Digital
 - (SDHC) Secure Digital
 - (MM) Multi - Media
 - (xD) xD - Picture Card
- ▶ MP3 PLAYERS
 - MP3 Player 320
 - MP3 Player 630
 - MP3 Player 650
 - MP3 Player 840
 - MP3 Player 850
 - MP3 Player 860 (NEW)
- ▶ USB FLASH DRIVES (High Speed)
 - JetFlash 110
 - JetFlash 130
 - JetFlash 150
 - JetFlash 160
 - JetFlash 168
 - JetFlash 185
 - JetFlash 2A
- ▶ USB FLASH DRIVES (Value Series)
 - JetFlash V10
 - JetFlash V15 (NEW)
 - JetFlash V20
 - JetFlash V30
 - JetFlash V33
 - JetFlash V35
 - JetFlash V60
 - JetFlash V85
 - JetFlash V90
 - JetFlash V95 (NEW)
 - JetFlash T3
 - JetFlash T5
 - JetFlash 220
- ▶ PHOTO STORAGE
 - Photo Frame 710
 - Photo Frame 720
 - Photo Frame 730 (NEW)
 - Photo Frame 810
 - Digital Album
- ▶ USB HARD DRIVES
 - StoreJet 18M/25M
 - StoreJet 25C
 - StoreJet 25F
 - StoreJet 25P
 - StoreJet 35U
 - StoreJet 2.5 IDE
 - StoreJet 2.5 SATA
- ▶ SOLID STATE DISKS
 - ExpressCard
 - Solid State HDD 1.8
 - SSD 2.5 (SATA) (NEW)
 - SSD 2.5 (IDE)
 - IDE Flash disk 2.5
 - SATA Flash Module
 - IDE USB Horizontal
 - IDE SSD 1.0
 - IDE 40 - Pin Vertical
 - IDE 44 - Pin Vertical
 - IDE 44 - Pin Horizontal
- ▶ PERIPHERALS
 - Card Readers (NEW)
 - PCMCIA Cards
 - PCMCIA Adapters
- ▶ ACCESSORIES
 - Cables/Headphones
 - JetFlash Caps

● **SOLID STATE DISKS** / IDE 40 -Pin Vertical / 4GB IDE Flash Module (40 -Pin Vertical)



Enlarge View

4GB IDE Flash Module (40 - Pin Vertical)

Product P/N: TS4GDOM40V - S

List Price: **\$62.60 (untaxed)**

Add to Cart

Also available in these capacities:
128MB / 256MB / 512MB / 1GB / 2GB / 4GB / 8GB / 16GB

- Forward
- Add to Wish
- Print
- Compatibility

▼ Product Information ▼ Shipping & Warranty

Transcend's IDE Flash Modules are specially designed for use in the demanding industrial environments where industrial PCs, Set Boxes and other computer systems must operate. IDE Flash Modules are a convenient and easy to use solution for expanding an industrial computer's memory capacity. - Top

Please Note:
This item comes "BULK" packaged for commercial use. Not Intended for Individual Retail Sale.

- Features:**
- Fully compatible with devices and O/S that support IDE standards (pitch=2.54mm)
 - Built -in ECC function assures high reliability of data transfers
 - LED indicates status of usage
 - The S series supports 50nm Flash
 - RoHS Compliant
 - Lower power consumption
 - 40 - Pin FEMALE connector**
 - 2-Year Warranty

- Specification:**
- Size: 61.0mm x 26.9mm x 7.1mm (with housing)
 - Op. Voltage: 3.3V / 5V
 - Op. Temperature: 0C (32F) to 7C (158F)
 - Durability: 10,000 insertion/removal cycles
 - Weight: 11g
 - Humidity: 5% to 95%
 - MTBF: 1,000,000 hours

- Accessories:**
- Power Adapter/Connector
 - Quick Installation Guide
 - Warranty Card

