



EDL Lighting Ltd



Line Drawing
when available

Version: Loading Bay-HTB-U-IP44-70W-24V

RS Order Code 794-3462

The Loading Bay is a powerful luminaire, ideal for those areas that require extra illumination. It is IP44 rated, and available in a range of arm configurations to suit your needs. It comes supplied with a 24v 70w halogen lamp, and can be mounted vertically

- Can be used in conjunction with the MT series of transformers.

Primary Voltage:	24v	Head Material:	Moulded plastic with steel bracket
Secondary Voltage:	not applicable	Shield Fitted:	Yes
Lamp type:	H3 Halogen	Shield material:	Polycarbonate
Wattage:	70w	Articulation movement:	Head to Base
Lamp base:	PK22S	Joint Type:	Friction
Switch Fitted:	yes	Trailing Cable:	Not Fitted
Switch Location:	On Head	Plug Fitted:	No
IP Rating:	IP 44	Manufacturing Standard:	BS EN 60598
Base Type:	Universal base	RHOS Compliant:	Yes
Base Fixing:	Can be vertical or horizontally mounted	Wee Compliant:	Not applicable
No of Arms:	0	Finish & Colour:	Black Plastic & Steel parts powder coated gunmetal
Length of Arms:	Head to Base No arms		
Arm Material:	Aluminium Knuckles		

EDL Lighting Limited, Redbrook lane, Brereton, Rugeley, Staffs WS15 1QU

Telephone: +44(0)1889 582112

Fax: +44(0)1889 584012

Email: sales@edl-lighting.co.uk Website www.edl-lighting.co.uk




EDL Lighting Ltd

Version: Loading Bay-HTB-U-IP44-70W-24V


RS Order Code 794-3462

Features:

High quality friction arm joints, move easily, yet retain position, tested to over 30,000 movements - Vibration resistant mountings and arms for demanding operating conditions - Versatile and flexible positioning, relative to subject, based on variety of arm length combinations - Cable is enclosed within base and arms - All metal parts are coated in tough chip resistant epoxy polyester powder paint - Switch is located on head for ease of use - The head is moulded from strong thermoplastic material - Units can be mounted on top of MT Series Transformers (see below for details range)



Accessories



Edge Clamp in gunmetal

Order Code: 500020AX000



H3 Halogen Lamp
available in


55w 12v order code: 017024XX000
70w 24v " " 017026XX000

Transformers:

The MT 60VA transformer series is designed for use with the Tasl 1, Task 21, Task 22 NT, Task 24 NT, and the Loading Bay (note: NT designates no internally fitted transformer. The MT transformer housing is pre-drilled to accept the EDL universal base)



Order Code	Primary Voltage	Secondary Voltage
MT5S	240v	12 / 24v ac
MT10S	240v	25 / 50v ac
MT15S	415v	12 / 24v ac
MT20S	415v	25 / 50v ac
MT25S	415v	110v ac



EDL Lighting Limited, Redbrook lane, Brereton, Rugeley, Staffs WS15 1QU

Telephone: +44(0)1889 582112

Fax: +44(0)1889 584012

Email: sales@edl-lighting.co.uk Website www.edl-lighting.co.uk