


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN)



METRIC

THIRD ANGLE
PROJECTION




- 1) PER PEZZI IN NASTRO
VEDERE DISEGNO 160429
(FOR STRIP VERSION
SEE DWG. 160429).
- 2) CONFEZIONATO IN ACCORDO ALLA
SPECIFICA AMP 107-20201.
(PACKAGED ACCORDING TO AMP SPEC. 107-20201).


3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI



SEZIONE A-A
(SECTION A-A)



SEZIONE B-B
(SECTION B-B)



3 OBSOLETE

STAGNATO (TIN PLATED)	BRONZO FOS. (PHOS. BRONZE)	5-160491-6	K
PRE NICHELATO (PRE-NICKEL PL.)	ACCIAIO (STEEL)	5-160491-4	K
STAGNATO (TIN PLATED)	OTTONE (BRASS)	5-160491-2	K
NUDO (PLAIN)	OTTONE (BRASS)	5-160491-1	K
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (AMP P/N)	REV

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES: UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE)	RANGO FILO (WIRE RANGE)	SCALA (SCALE)
± 0.3	3.0-4.0	1.0-2.5	4:1

ANGOLI (ANGLES)	± 2°	AMP AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)
--------------------	------	--

K1	REVISED PER ECO-09-022178	KK	24 SEP 09	DIS. 02 NOV 2000 (DR.) H. YAALI	DESCRIZIONE (DESCRIPTION) FASTON® Connector, .187" sr. REC. CONTACT (LOOSE PIECE VERSION)
K	FIRST EMISSION ET00-0198-01	H.Y.	27 JUL 2001	CONT. 02 NOV 2000 (CHK) C. TARTARI	LOC. SIZE NUMERO (DWG NO)
REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR) (DATE)	APP. (APP.)	I A3	C-160491
				REV. K1	FOGLIO (SHEET) 1 DI 1 (OF)