


Electrical Component Markers

B-412 Polypropylene, B-499 White/Yellow Nylon Cloth

Diagram	Order Reference	Labels Per Roll	Label Dimensions Width A (mm)	Label Dimensions Height B (mm)	Maximum Characters Per Line For Font: 2	Maximum Lines Of Text For Font: 2
▲	PTL-41-499-YL	750	16	5	15	1
▲	PTL-47-499-YL	750	20.00	8.00	18	2
●	PTL-57-412	Cont.	12.70	15.24 m	50	5
▲	PTL-67-499-YL	750	15.00	9.00	13	2
▲	BPTL-67-499-YL	7 500	15.00	9.00	13	2
■	PTL-82-499	500	9.53 diameter		8	1
■	PTL-82-499YL	500	9.53 diameter		8	1
■	PTL-83-499	500	12.70 diameter		11	1
■	PTL-83-499YL	500	12.70 diameter		11	1




EPREP Labels Available to Print with TLS2200®/TLS PC LINK™

B-7593 Polyester Tag laminated onto foam carrier

BRADY EPREP (Engraved Plate Replacement) labels are innovative labels specifically designed to replace engraved and plotted plates for identification of electrical components, electrical cabinets, push buttons, patch panels etc.



Diagram	Order Reference	Markers Per Roll	Colour	Dimensions		
				Width A (mm)	Height B (mm)	Diameter (mm)
●	PTLEP-01-7593-WT	250	White	27	8	
●	PTLEP-01-7593-SV	250	Silver	27	8	
●	PTLEP-01-7593-BK	250	Black	27	8	
●	PTLEP-01-7593-RD	250	Red	27	8	
●	PTLEP-01-7593-GR	250	Green	27	8	
●	PTLEP-01-7593-YL	250	Yellow	27	8	
●	PTLEP-02-7593-WT	250	White	27	12.5	
●	PTLEP-02-7593-SV	250	Silver	27	12.5	
●	PTLEP-02-7593-BK	250	Black	27	12.5	
●	PTLEP-02-7593-RD	250	Red	27	12.5	
●	PTLEP-02-7593-GR	250	Green	27	12.5	
●	PTLEP-02-7593-YL	250	Yellow	27	12.5	
●	PTLEP-03-7593-WT	150	White	27	15	
●	PTLEP-03-7593-SV	150	Silver	27	15	
●	PTLEP-03-7593-BK	150	Black	27	15	
●	PTLEP-03-7593-RD	150	Red	27	15	
●	PTLEP-03-7593-GR	150	Green	27	15	
●	PTLEP-03-7593-YL	150	Yellow	27	15	
●	PTLEP-04-7593-WT	150	White	27	18	
●	PTLEP-04-7593-SV	150	Silver	27	18	
●	PTLEP-04-7593-BK	150	Black	27	18	
●	PTLEP-04-7593-RD	150	Red	27	18	
●	PTLEP-04-7593-GR	150	Green	27	18	
●	PTLEP-04-7593-YL	150	Yellow	27	18	
▲	PTLEP-05-7593-BK	500	Black	30	40	24
▲	PTLEP-05-7593-GR	500	Green	30	40	24
▲	PTLEP-05-7593-RD	500	Red	30	40	24
▲	PTLEP-05-7593-SV	500	Silver	30	40	24
▲	PTLEP-05-7593-WT	500	White	30	40	24
▲	PTLEP-05-7593-YL	500	Yellow	30	40	24
●	PTLEP-06-7593-BK	500	Black	45	15	
●	PTLEP-06-7593-RD	500	Red	45	15	
●	BPTLEP-06-7593-SV	500	Silver	45	15	
●	BPTLEP-06-7593-WT	500	White	45	15	
●	PTLEP-06-7593-YL	500	Yellow	45	15	
●	PTLEP-07-7593-WT	100	White	35	18	
●	PTLEP-07-7593-SV	100	Silver	35	18	
●	PTLEP-07-7593-BK	100	Black	35	18	
●	PTLEP-07-7593-YL	100	Yellow	35	18	
●	PTLEP-08-7593-WT	100	White	48	19	
●	PTLEP-08-7593-SV	100	Silver	48	19	
●	PTLEP-08-7593-BK	100	Black	48	19	
●	PTLEP-08-7593-YL	100	Yellow	48	19	
●	PTLEP-09-7593-WT	100	White	25	75	
●	PTLEP-09-7593-YL	100	Yellow	25	75	
●	PTLEP-10-7593-WT	100	White	25	100	
●	PTLEP-10-7593-YL	100	Yellow	25	100	



For printing these parts on a TLS2200® & TLS PC LINK™ you will need ribbon R-6010 (Black), R-4410W (White), R-4410B (Blue) or R-4410R (Red)

For further information on Custom EPREP Labels, please visit our website www.bradyeurope.com