


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35746-0110](#)
Status: **Active**
Overview: [VersaBlade™ Wire-to-Wire Connector System](#)
Description: [VersaBlade™ .070 Female Crimp Terminal, 20-22 AWG, Type A](#)

Documents:

3D Model	Product Specification PS-35180-003 (PDF)
Drawing (PDF)	Product Specification PS-35182-003 (PDF)
Product Specification PS-35150-001 (PDF)	Packaging Specification PK-35746-001 (PDF)
Product Specification PS-35180-002 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	35746
Application	Power
Crimp Quality Equipment	Yes
Overview	VersaBlade™ Wire-to-Wire Connector System
Product Name	VersaBlade™
UPC	800753856417

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	20, 22
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35746-001
Product Specification	PS-35150-001, PS-35180-002, PS-35180-003, PS-35182-003
Sales Drawing	SD-35746-001

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[35746Series](#)

Mates With

[35745 Crimp Terminal](#)

Use With

[35150 VersaBlade™ Hybrid Receptacle Housing](#). [35151 VersaBlade™ Hybrid Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
T2 Terminator Die	0638529000
Hand Crimp Tool for Industry standard 1.78mm Terminals	0638196800

FineAdjust™	<u>0638629000</u>
Applicator	
Extraction Tool	<u>0638132700</u>

This document was generated on 03/02/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION