

A907 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A907*1.0	PFX Drills, Jobber Length	HSCo	BRIGHT	12	34	1
A907*1.1	PFX Drills, Jobber Length	HSCo	BRIGHT	14	36	1.1
A907*1.2	PFX Drills, Jobber Length	HSCo	BRIGHT	16	38	1.2
A907*1.3	PFX Drills, Jobber Length	HSCo	BRIGHT	16	38	1.3
A907*1.4	PFX Drills, Jobber Length	HSCo	BRIGHT	18	40	1.4
A907*1.5	PFX Drills, Jobber Length	HSCo	BRIGHT	18	40	1.5
A907*1/16	PFX Drills, Jobber Length	HSCo	BRIGHT	20	43	1.59
A907*1.6	PFX Drills, Jobber Length	HSCo	BRIGHT	20	43	1.6
A907*1.7	PFX Drills, Jobber Length	HSCo	BRIGHT	20	43	1.7
A907*1.8	PFX Drills, Jobber Length	HSCo	BRIGHT	22	46	1.8
A907*1.9	PFX Drills, Jobber Length	HSCo	BRIGHT	22	46	1.9
A907*5/64	PFX Drills, Jobber Length	HSCo	BRIGHT	24	49	1.98
A907*2.0	PFX Drills, Jobber Length	HSCo	BRIGHT	24	49	2
A907*2.1	PFX Drills, Jobber Length	HSCo	BRIGHT	24	49	2.1
A907*2.2	PFX Drills, Jobber Length	HSCo	BRIGHT	27	53	2.2
A907*2.3	PFX Drills, Jobber Length	HSCo	BRIGHT	27	53	2.3
A907*3/32	PFX Drills, Jobber Length	HSCo	BRIGHT	30	57	2.38
A907*2.4	PFX Drills, Jobber Length	HSCo	BRIGHT	30	57	2.4
A907*2.5	PFX Drills, Jobber Length	HSCo	BRIGHT	30	57	2.5
A907*2.6	PFX Drills, Jobber Length	HSCo	BRIGHT	30	57	2.6
A907*2.7	PFX Drills, Jobber Length	HSCo	BRIGHT	33	61	2.7
A907*7/64	PFX Drills, Jobber Length	HSCo	BRIGHT	33	61	2.78
A907*2.8	PFX Drills, Jobber Length	HSCo	BRIGHT	33	61	2.8
A907*2.9	PFX Drills, Jobber Length	HSCo	BRIGHT	33	61	2.9
A907*3.0	PFX Drills, Jobber Length	HSCo	BRIGHT	33	61	3
A907*3.1	PFX Drills, Jobber Length	HSCo	BRIGHT	36	65	3.1
A907*1/8	PFX Drills, Jobber Length	HSCo	BRIGHT	36	65	3.18
A907*3.2	PFX Drills, Jobber Length	HSCo	BRIGHT	36	65	3.2
A907*3.3	PFX Drills, Jobber Length	HSCo	BRIGHT	36	65	3.3
A907*3.4	PFX Drills, Jobber Length	HSCo	BRIGHT	39	70	3.4
A907*3.5	PFX Drills, Jobber Length	HSCo	BRIGHT	39	70	3.5
A907*9/64	PFX Drills, Jobber Length	HSCo	BRIGHT	39	70	3.57
A907*3.6	PFX Drills, Jobber Length	HSCo	BRIGHT	39	70	3.6
A907*3.7	PFX Drills, Jobber Length	HSCo	BRIGHT	39	70	3.7
A907*3.8	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	3.8
A907*3.9	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	3.9
A907*5/32	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	3.97
A907*4.0	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	4
A907*4.1	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	4.1
A907*4.2	PFX Drills, Jobber Length	HSCo	BRIGHT	43	75	4.2
A907*4.3	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.3
A907*11/64	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.37
A907*4.4	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.4
A907*4.5	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.5
A907*4.6	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.6
A907*4.7	PFX Drills, Jobber Length	HSCo	BRIGHT	47	80	4.7
A907*3/16	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	4.76
A907*4.8	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	4.8
A907*4.9	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	4.9

A907 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A907*5.0	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	5
A907*5.1	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	5.1
A907*13/64	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	5.16
A907*5.2	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	5.2
A907*5.3	PFX Drills, Jobber Length	HSCo	BRIGHT	52	86	5.3
A907*5.4	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.4
A907*5.5	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.5
A907*7/32	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.56
A907*5.6	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.6
A907*5.7	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.7
A907*5.8	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.8
A907*5.9	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.9
A907*15/64	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	5.95
A907*6.0	PFX Drills, Jobber Length	HSCo	BRIGHT	57	93	6
A907*6.1	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.1
A907*6.2	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.2
A907*6.3	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.3
A907*1/4	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.35
A907*6.4	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.4
A907*6.5	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.5
A907*6.6	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.6
A907*6.7	PFX Drills, Jobber Length	HSCo	BRIGHT	63	101	6.7
A907*17/64	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	6.75
A907*6.8	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	6.8
A907*6.9	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	6.9
A907*7.0	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7
A907*7.1	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.1
A907*9/32	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.14
A907*7.2	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.2
A907*7.3	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.3
A907*7.4	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.4
A907*7.5	PFX Drills, Jobber Length	HSCo	BRIGHT	69	109	7.5
A907*19/64	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.54
A907*7.6	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.6
A907*7.7	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.7
A907*7.8	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.8
A907*7.9	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.9
A907*5/16	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	7.94
A907*8.0	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8
A907*8.1	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.1
A907*8.2	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.2
A907*8.3	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.3
A907*21/64	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.33
A907*8.4	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.4
A907*8.5	PFX Drills, Jobber Length	HSCo	BRIGHT	75	117	8.5
A907*8.6	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	8.6
A907*8.7	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	8.7
A907*11/32	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	8.73
A907*8.8	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	8.8

A907 Series Drills Specification

Part No.	Description	Material	Finish	Flute Length	Overall Length	Manf. Dia.
A907*8.9	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	8.9
A907*9.0	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9
A907*9.1	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.1
A907*23/64	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.13
A907*9.2	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.2
A907*9.3	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.3
A907*9.4	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.4
A907*9.5	PFX Drills, Jobber Length	HSCo	BRIGHT	81	125	9.5
A907*3/8	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.53
A907*9.6	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.6
A907*9.7	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.7
A907*9.8	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.8
A907*9.9	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.9
A907*25/64	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	9.92
A907*10.0	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10
A907*10.2	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10.2
A907*10.3	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10.3
A907*13/32	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10.32
A907*10.4	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10.4
A907*10.5	PFX Drills, Jobber Length	HSCo	BRIGHT	87	133	10.5
A907*27/64	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	10.72
A907*10.8	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	10.8
A907*11.0	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11
A907*7/16	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11.11
A907*11.2	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11.2
A907*11.5	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11.5
A907*29/64	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11.51
A907*11.8	PFX Drills, Jobber Length	HSCo	BRIGHT	97	142	11.8
A907*15/32	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	11.91
A907*12.0	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12
A907*12.2	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12.2
A907*31/64	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12.3
A907*12.5	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12.5
A907*1/2	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12.7
A907*12.8	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	12.8
A907*13.0	PFX Drills, Jobber Length	HSCo	BRIGHT	106	151	13
A907*14.0	PFX Drills, Jobber Length	HSCo	BRIGHT	115	160	14