

## Plastic label - US-EMLF (104X70) BU - 1014296

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Plastic label, Card, blue, unlabeled, can be labeled with: THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 104 x 70 mm




The figure shows a version of the article

### Why buy this product

- Stick-on combi labels
- Suitable for indoor and outdoor use
- The markers conform to the ISO 7010 international standard
- High adhesive strength
- When used in conjunction with high-quality ink ribbons, they result in a highly resistant form of marking that is even suitable for harsh environments
- The perforated markers are easy to separate



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 786683
Weight per Piece (excluding packing)	5.04 g
Custom tariff number	39203000
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	104 mm
Width (a)	70 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

#### General

# Plastic label - US-EMLF (104X70) BU - 1014296

## Technical data

### General

Color	blue
Type	Rectangle
Components	Silicone-free
Material	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2
Marking mounting type	Adhesive

## Classifications

### eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Accessories

### Accessories

#### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

## Plastic label - US-EMLF (104X70) BU - 1014296

### Accessories

Ink ribbon - TM-RIBBON 110-TC/TR WH - 1014402



Ink ribbon, Length: 240000 mm, Color: white

---

Ink ribbon - TM-RIBBON 110-TC BK/RD - 1014403



Ink ribbon, Length: 60000 mm, Color: black/red

---

Ink ribbon - TM-RIBBON 110-TC BK/RD/YE - 1014404



Ink ribbon, Length: 60000 mm, Color: black/red/yellow

---

Ink ribbon - TM-RIBBON 110-TC BK/RD/BU/YE - 1014405



Ink ribbon, Length: 60000 mm, Color: black/red/blue/yellow

---

### Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

---