



CorePro LEDbulb

CorePro LEDBulb 7.5-48W E27 830

Delivering a warm, halogen-like accent beam, LEDspots are a perfect fit for spot lighting and have a broad compatibility with transformers. LEDspots are compatible with most existing fixtures with a GU10 / MR16 GU5.3 / E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs. LEDcandle and LEDluster are compatible with existing fixtures with an E27/E14 holder and are designed for retrofit replacement of incandescent lamps. LEDlamps deliver huge energy savings and minimize maintenance cost



PHILIPS

Product data

• General Characteristics

Cap-Base	ES
Bulb	A60 [A 60mm]
Rated Lifetime	15000 hr
Nominal Lifetime	15000 hr
hours	

• Light Technical Characteristics

Colour Code	830
Colour Designation	White
Correlated Colour	3000 K
Temperature	
Luminous Flux	600 Lm
Colour rendering	80
index	
Luminous Efficacy	80.00 Lm/W
Lamp	
Colour Temperature	3000 K [CCT 3000K]
Rated Luminous Flux	600 Lm
LLMF - end nominal	70 %
lifetime	
Colour consistency	6 steps

• Electrical Characteristics

Wattage	7.5 W
Voltage	220-240 V
Line Frequency	50-60 Hz
Power Factor	0.7 -
Lamp Current mA	50 mA
Dimmable	No
Wattage Equivalent	48 W
Rated Wattage	7.5 W
Starting Time	0.5 s
Suitable for accent	No
lighting	

• Temperature Characteristics

T-case maximum	75 C
----------------	------

• Environmental characteristics

Energy Efficiency	A+
Label (EEL)	

• Measuring Conditions

Switching cycle	50000X
-----------------	--------


• Product Dimensions

Overall Length C	102.6 mm
Diameter D	56.3 mm

• Product Data

Order code	754237 00
Full product code	871829175423700
Full product name	CorePro LEDBulb 7.5-48W E27 830
Order product name	CorePro LEDBulb 7.5-48W E27 830
Pieces per pack	1
Packing configuration	6
Packs per outerbox	6
Bar code on pack -	8718291754237
EAN1	
Bar code on	8718291754244
outerbox - EAN3	
Logistic code(s) -	929000248832
12NC	
Net weight per piece	0.081 kg

Photometric data



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, August 3
data subject to change