

End clamp - E/MBK - 1401637

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

End clamp, width: 6.2 mm, color: gray




Why buy this product

- Can be screwed onto NS 15 DIN rails
- Can be mounted directly on the mounting plate as an MBK terminal block base
- Large-surface labeling



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 100 pc |
| GTIN |  4 017918 020484 |
| Weight per Piece (excluding packing) | 1.62 g |
| Custom tariff number | 39269097 |
| Country of origin | Poland |

Technical data

Dimensions

| | |
|--------|---------|
| Height | 11.4 mm |
| Length | 22 mm |
| Width | 6.1 mm |

General

| | |
|----------|--------------------|
| Material | PA |
| Coating | 3.2 mm fixing hole |
| Color | gray |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
|------------|----------|

End clamp - E/MBK - 1401637

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141135 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141135 |
| eCl@ss 7.0 | 27141135 |
| eCl@ss 8.0 | 27141135 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC001041 |
| ETIM 4.0 | EC001041 |
| ETIM 5.0 | EC001041 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 39121708 |
| UNSPSC 11 | 39121708 |
| UNSPSC 12.01 | 39121708 |
| UNSPSC 13.2 | 39121708 |

Accessories

Accessories

Mounting rail

DIN rail, unperforated - NS 15 UNPERF 2000MM - 1401695



DIN rail, material: Steel, unperforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 PERF 2000MM - 1401682



DIN rail, material: steel galvanized and passivated with a thick layer, perforated, height 5.5 mm, width 15 mm, length: 2000 mm

End clamp - E/MBK - 1401637

Accessories

DIN rail perforated - NS 15 AL PERF 2000MM - 1401763



DIN rail, material: Aluminum, perforated, height 5.5 mm, width 15 mm, length: 2 m

DIN rail perforated - NS 15 WH PERF 2000MM - 1204096



DIN rail, material: steel, perforated, height 5.5 mm, width 15 mm, length: 2 m

Drawings

End clamp - E/MBK - 1401637

Dimensioned drawing

