

GEO MAINS FREE SOLAR LIGHTING KITS

Our Geo Mains Free Solar Lighting Kits provide light and power to locations without mains power or where cost effective environmentally friendly power solutions are preferred.

Installing a mains power supply to remote locations isn't always possible and is often highly expensive when it is.

Geo Mains Free Solar Lighting Kits can be installed by anyone with basic DIY skills and are exempt from Part P of the building regulations which means there is no need to pay an electrician to have your kit installed or certified.

Comparison Chart

Product Name	GEO 1	GEO 2
Bulb(s) 3w (40watt equivalent)	1	2
Max Runtime (hours) *	48	68
Average Nightly Runtime (hours) **	6.5	6.5
Area Lit (Sq m)	16	32
Switch	Wall	Wall
Recommended Battery (Ah)	12	34
Cable provided (metres)	5	5
Solar Panel (watts)	5w	10w
Installation time (minutes)	60	60

* based on fully charged battery

** based on 4 hrs charge

GEO 1 MAINS FREE SOLAR LIGHTING KIT

The Geo 1 comes with a single 3W LED bulb suitable for lighting an area of up to 16 square metres making it ideal for medium sized rooms, sheds, garages, outhouses, Wendy houses, greenhouses and tree houses.

Kit includes:

- 1 x 5W solar panel
- 2 x crocodile clips
- 2 x fuse holders
- 2 x 5a fuse
- 6 x ring terminals
- 8 x cable clips
- 1 x light bulb holder
- 1 x light switch box
- 2 x connection blocks
- 4 x screws
- 4 x roof fixing blocks
- 1 x 5m run of cable
- 1 x 3W LED bulbs
- 4 x cable ties

Specifications

Solar Panel Size: **H: 250mm x W: 200mm**

Panel Wattage: **5W**

Boxed Weight: **2kg**



GEO 1
SOLAR LIGHTING KIT™

Product Code: SS9048

GEO 2 MAINS FREE SOLAR LIGHTING KIT

The Geo 2 comes with two 3W LED bulbs suitable for lighting an area of up to 32 square metres making it ideal for medium / large sized rooms, sheds, garages, outhouses, Wendy houses and tree houses.

Kit includes:

- 1 x 10W solar panel
- 2 x crocodile clips
- 2 x fuse holders
- 2 x 5a fuse
- 6 x ring terminals
- 8 x cable clips
- 2 x light bulb holder
- 1 x light switch box
- 2 x connection blocks
- 4 x screws
- 4 x roof fixing blocks
- 1 x 5m run of cable
- 2 x 3W LED bulbs
- 4 x cable ties

Specifications

Solar Panel Size: **H: 350mm x W: 290mm**

Panel Wattage: **10W**

Boxed Weight: **3kg**



GEO 2
SOLAR LIGHTING KIT™

Product Code: SS9049