

Classic ECO Ball

CLECO BAL 240V 18W B22 SV1

0023144

Range features



PRODUCT OVERVIEW

Ordering number	0023144
Light colour	828 Homelight
Technology	Halogen
Energy class	D
Average life (Rated) (h)	2000
Lamp finish	Clear
Lamp shape	Ball
Dimmable	Yes
Cap/Base	B22
Type	Ball ECO
EAN code	5410288231440
CRI (Ra)	100
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	180
Watt (Nominal) (W)	18
Equivalent watt (W)	21
Voltage (V)	240

Classic ECO Ball

CLECO BAL 240V 18W B22 SV1

0023144

DATA TABLE

General data

Ordering number	0023144
Technology	Halogen
Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000
Energy saving lamp	No
Energy class	D
Lamp shape	Ball
Lamp finish	Clear
Dimmable	Yes
Cap/Base	B22
Type	Ball ECO
EAN code	5410288231440
Product name	CLECO BAL 240V 18W B22 SV1
Lamp mercury content (mg)	0
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Control gear required	No
Fixture rating	Open
IEC Reference	IEC 60357
IEC Reference 2	IEC 60432-2
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	> 8000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	828 Homelight
CRI (Ra)	100
Suitable for accent lighting	No
Beam angle(°)	na
Colour temperature (K)	2800
Luminous flux (Rated) (lm)	180
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	180

Classic ECO Ball

CLECO BAL 240V 18W B22 SV1

0023144

Electrical data

kWh per 1000 hours burning time	18
Watt (Rated) (W)	18
Watt (Nominal) (W)	18
Equivalent watt (W)	21
Voltage (V)	240
Lamp power factor	1

Physical data


Weight (kg)	0.02
Lamp Length (mm) - C/L	72.5
Max. Lamp Diameter (mm) - D	46
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	7.60 x 4.55 x 4.55
Inner package dimensions (L x W x H) (cm)	23.50 x 10.00 x 8.50
Inner package net weight (kg)	0.19
Outer package dimensions (L x W x H) (cm)	52.00 x 25.50 x 19.00

Classic ECO Ball

CLECO BAL 240V 18W B22 SV1

0023144

TECHNICAL DRAWINGS



ENERGY LABEL

