

Relay socket - PR3-BSC1/2X21 - 2833602

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Relay socket PR3..., for octal relay REL-OR with 2 PDT, screw connections, connection facility for input/interference suppression modules, for mounting on NS 35/7.5




Why buy this product

- ✓ Relay base family that can be fitted with 2 PDT or 3 PDT relays



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 933821
Weight per Piece (excluding packing)	60.57 g
Custom tariff number	85366990
Country of origin	China

Technical data

Dimensions

Width	38 mm
Height	75 mm
Depth with retaining bracket	84 mm (EL3-M52)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²

Relay socket - PR3-BSC1/2X21 - 2833602

Technical data

Connection data

Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
2 conductors with same cross section, solid max.	2.50 mm ²
2 conductors with same cross section, stranded max.	2.50 mm ²
2 conductors with same cross section, AWG max.	14
Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3

General

Nominal voltage U _N	400 V AC/DC
Nominal current I _N	10 A
Color	green

Classifications

eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

ETIM

ETIM 2.0	EC001456
ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001456

UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39121516

Approvals

Approvals

Relay socket - PR3-BSC1/2X21 - 2833602

Approvals

Approvals

UL Recognized / cUL Recognized / CSA / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized

cUL Recognized

CSA

cULus Recognized

Accessories

Necessary add-on products

Single relay - REL-OR- 24DC/2X21 - 2834232



Pluggable octal relay with power contacts, 2 PDT, test button, mechanical switching position indication, coil voltage 24 V DC

Relay socket - PR3-BSC1/2X21 - 2833602

Accessories

Single relay - REL-OR- 24AC/2X21 - 2834245



Pluggable octal relay with power contacts, 2 PDT, test button, mechanical switching position indication, coil voltage 24 V AC

Single relay - REL-OR-120AC/2X21 - 2834258



Pluggable octal relay with power contacts, 2 PDT, test button, mechanical switching position indication, coil voltage 120 V AC

Single relay - REL-OR-230AC/2X21 - 2834261



Pluggable octal relay with power contacts, 2 PDT, test button, mechanical switching position indication, coil voltage 230 V AC
