

# SCSICONNECT | 2904 KIT

Ideal for SCSI CD or DVD-Recorders

## Product Highlights

- Reliable CD/DVD Creation with SCSI BusMastering
- Connect up to 7 Peripherals
- Plug-and-Play Installation

### Get Ready to Record High-Quality CDs or DVDs

With your recording software (not included in this kit) and your SCSI CD-R/RW drive or DVD recorder, burn all your CDs or DVDs faster and better with the SCSIconnect 2904.


### Best Overall System

#### Performance and Reliability

The combination of a Fast SCSI data transfer and low CPU utilization add up to increased efficiency and reliability when transferring data. For example you can use your full CPU power for other applications while burning a CD/DVD.

#### Connect up to 7 Peripherals with One Card

Add up to seven peripherals just by daisy-chaining them together. This SCSIconnect 2904 is ideal for CD-ROM drives and recorders, DVD-ROM drives and recorders, removable drives and scanners.




### Install with Plug-and-Play Ease

Installation is a snap. Just remove your computer's case, slide the card into your PCI expansion slot, and connect the SCSI peripherals. There are no jumpers or switches to set – the Plug-and-Play feature does the rest.

### Trust Adaptec – the World's #1 Choice for SCSI Cards

Adaptec is the industry standard for SCSI cards. And Adaptec SCSI Cards are backed by a 5-year warranty.

### SCSI Performs Up to 38% Faster than An IDE Connection



Benchmark configuration:  
300MHz PII system with 64 MB RAM, Windows 98 and Adaptec Easy CD Creator V.3.5a.  
Copying data to IDE hard drive then copying data to (SCSI or IDE) 4X CD-recorder.

**Adaptec European  
Headquarters**

Drève Richelle 161, BP 8  
B-1410 Waterloo  
Belgium  
Tel.: +32.2.352.34.11  
Fax: +32.2.352.34.00

**Adaptec  
Central European Sales Office**

Richard-Reitzner-Allee 8  
D-85540 Haar  
Germany  
Tel.: +49.89.456.40.60  
Fax: +49.89.456.406.15

**Adaptec  
Southern European Sales Office**

Parc d'Activités Parkile  
164/166 avenue Joseph Kessel  
F-78960 Voisins-le-Bretonneux  
France  
Tel.: +33.1.34.52.34.34  
Fax: +33.1.34.52.34.32

**Adaptec  
Northern European Sales Office**

4 Archipelago  
Lyon Way, Camberley,  
GB-Surrey GU16 5ER  
United Kingdom  
Tel.: +44.1276.854.500  
Fax: +44.1276.854.505

**World Wide Web**  
<http://www.adaptec-europe.com>

**Adaptec, Inc.**  
691 South Milpitas Boulevard  
Milpitas, California 95035  
USA

Copyright 2001 Adaptec, Inc. All rights reserved.  
Adaptec, the Adaptec logo, the Adaptec tagline,  
Easy CD Creator, and AVA are trademarks of  
Adaptec, Inc., which may be registered in some  
jurisdictions. Windows 95, Windows 98, Windows Me,  
Windows NT and Windows 2000 are registered  
trademarks of Microsoft Corporation, used under  
license. All other trademarks used are owned by  
their respective owners.

## Technical Specifications

Operating Systems Supported:	DOS®, Windows® 95/98/Me/NT/2000
PC Bus Type:	32-bit PCI
Interface Transfer Method:	Bus Master DMA (Direct Memory Access)
Data Transfer Rate:	10 MB/sec
Supported Protocol:	SCSI-1, SCSI-2, and Fast SCSI-2
Peripheral Support:	Non-bootable
Total Devices Supported:	7 total (internal or external)
External Connector:	50-pin high-density SCSI-2 (female)
Internal Connector:	50-pin standard (male)

## Recommended Minimum System Requirements

- IBM-compatible PC – 486, Pentium or above
- DOS®, Windows® 95/98/Me/NT/2000 Operating System
- PCI expansion slot
- SCSI Device

## Complete Kit Contents

- AVA™-2904 SCSI Card
- Standard, 3-position internal SCSI ribbon cable
- Complete documentation

