

0,80mm BASIC SOCKET BSE SERIES

SPECIFICATIONS

For complete specifications see www.samtec.com?BSE

Insulator Material:

Liquid Crystal

Polymer

Contact Material:

Phosphor Bronze

Current Rating:

2A @ 80°C ambient mated with BTE & 5mm Stack Height

Operating Temp Range:

-65°C to +125°C

Voltage Rating:

225 VAC mated with BTE

& 5mm Stack Height

Plating:

Au over 50µ" (1,27µm) Ni




Mates with:
BTE

STACK HEIGHT CAPABILITY

LEAD STYLE	MATED HEIGHT WITH BTE
-01	(5,00) .197
-02	(8,00) .315
-03	(11,00) .433
-04	(16,10) .634
-05	(19,10) .752

14mm, 22mm, 25mm and 30mm stack height capability. Call for availability.



APPLICATION SPECIFIC OPTION

30µ" (0,76µm) Gold and Friction Lock options available. Call Samtec.



Note: Some lengths, styles and options are non-standard, non-returnable.

Processing:

Max Processing Temp:

230°C for 60 seconds

SMT Lead Coplanarity:

(0,10mm) .004" max (020-080)

(0,15mm) .006" max (100-120)

Suggested Paste Thickness:




For most applications add (0,05mm) .002" to max SMT lead coplanarity

Board Stacking:

Maximum two connectors per board recommended. For applications requiring more contact ipg@samtec.com

Suggested PCB Layouts:

For reference only. Go to www.samtec.com?BSE for recommended PCB layout.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
 SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315 SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
 SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-87420413 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502 SAMTEC JAPAN • Tel: 81-424-42-8318 • Fax: 81-424-42-8319
 SAMTEC CHINA • Tel: 86-21-5385-4089 • Fax: 86-21-5385-4047 SAMTEC TAIWAN • Tel: 886-02-2364-6077 • Fax: 886-02-2367-9531
 SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745