© 1980年 日本エー・エム・ピー株式会社
AMP 社の諸製品は特許又は特許出願中
© 1980 BY AMP (Japan) Ltd.
ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING









寸法公差は ±0.20
(TOLERANCE : ±0.2)
パネル取付穴
(DIMENSION OF PANEL)



NOTES;
1. APPLIED CONTACT P/N : 170359, 170360, 170361, 170362.
2. MATING CONN ; PLUG HOUSING P/N 172338.
3. PANEL THICKNESS ; 0.8 ~ 2.0 mm
4. PRESS DIRECTION OF PANEL MUST BE SAME AS HOUSING INSERTED DIRECTION.
5. INSTRUCTION SHEET ; IS-105J
6. PRODUCT SPEC : 108-5151.
7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注;
1. 使用端子型番は、170359, 170360, 170361, 170362
2. 嵌合相手ハウジング型番は、172338
3. 適用パネル厚 0.8 ~ 2.0 mm.
4. 取付穴打抜方向とハウジングの挿入方向は同じである。
5. 取扱説明書 : IS-105J
6. 適用製品仕様書: 108-5151

7 OBSOLETE

色 (COLOR)	型番 (P/N)
黄 (YELLOW)	1-172330-4
黒 (BLACK)	1-172330-9
青 (BLUE)	1-172330-6
緑 (GREEN)	1-172330-5
赤 (RED)	1-172330-2
自然色 (NATURAL)	172330-1

LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE
A2	ECO-10-000444	KK	AEG	JAN 10
A1	黄色 追加 J-10297	T.O	M.S	9/22/80
A	変更 J-9972	A.K	[illegible]	8/31/80
0,	変更 J81-5998	K.Y	Z.T	4/21/81
0	作成 J80-5988	K.Y	Z.T	10/20/80

材料 (MATERIAL)
6/6ナイロン(UL94V-2)
(NYLON 6/6 UL 94V-2)

一般公差
TOLERANCE EXCEPT AS NOTED ±0.3 ±1°

仕上 (FINISH)
色 ; 表参照
HOUSING COLOR : SEE TABLE

DR. K. Yuasa 4/20/81
CHK.
DE. T. Tanifuji 4/21/81
APP.

AMP 日本エー・エム・ピー株式会社 TOKYO, JAPAN

名称 (NAME) MINI-UNIVERSAL MATE-N-LOK CONN. CAP HOUSING 4 Pos. (UL 94V-2)
4極ミニ ユニバーサル メイテン ロック コネクタ キャップ ハウジング (UL94V-2)

SIZE B | LOC J | 番号 (NO.) C-172330
尺度 (SCALE) 2 : 1 | REV. A2 | SHEET —

(CUSTOMER DRAWING) 参考図面