

Accessory Kits

Cleaning / Polishing Set (684)

All you need for cleaning and polishing in a convenient box. Removable accessory tray and 3 dividers provide perfect storage solution. Dremel Quick Start leaflet explains the included accessories.



Included accessories

Cleaning / Polishing

403, 404, 405, 428, 520, 414(6), 422, 425(2), 429(3), 421

Collets / Mandrels / Miscellaneous

401, 402

Order information

Ordernumber: 26150684JA

EAN: 8710364029099

Multipurpose Set (687)

Assortment of best selling accessories in a convenient box. Removable accessory tray and 3 dividers provide perfect storage solution. Dremel Quick Start leaflet explains the included accessories.



Included accessories

Carving / Engraving / Routing

194

Grinding / Sharpening

952, 85422

Cleaning / Polishing

403, 414(2), 429(2), 421

Cutting

409(36), 426

Sanding

407, 408, 432(2)

Collets / Mandrels / Miscellaneous

401, 402

Order information

Ordernumber: 26150687JA

EAN: 8710364029105

Carving / Engraving / Routing

1. Engraving Cutters




Quality cutters for detail engraving, carving, routing in wood, fiberglass, plastic and soft metals.



Model	Quantity	Working $\varnothing$ mm	Shank $\varnothing$ mm	Ordernumber	EAN
105	1	0.8	2.4	2615010532	8710364007288
106	1	1.6	2.4	2615010632	8710364007295
107	1	2.4	2.4	2615010732	8710364007301
108	1	0.8	2.4	2615010832	8710364007318
110	1	1.9	2.4	2615011032	8710364007820
111	1	0.8	2.4	2615011132	8710364007837
113	1	1.6	2.4	2615011332	8710364007325

2. High Speed Cutters



High speed cutters can be used for shaping, hollowing, grooving, slotting, making tapered holes in soft metals, plastics and woods.



Model	Quantity	Working $\varnothing$ mm	Shank $\varnothing$ mm	Ordernumber	EAN
114	1	7.8	3.2	2615011432	8710364007868
196	1	5.6	3.2	2615019632	8710364007394
199	1	9.5	3.2	2615019932	8710364007400
194	1	3.2	3.2	2615019432	8710364007387
115	1	7.8	3.2	2615011532	8710364007332
117	1	6.4	3.2	2615011732	8710364007875
118	1	3.2	3.2	2615011832	8710364007349
125	1	6.4	3.2	2615012532	8710364007356
134	1	7.2	3.2	2615013432	8710364007912
144	1	7.8	3.2	2615014432	8710364007936
192	1	4.8	3.2	2615019232	8710364007363
193	1	2.0	3.2	2615019332	8710364007370

Grinding / Sharpening

1. Aluminum Oxide Grinding Wheel



541

Use for deburring, rust removal and general purpose grinding. Use with mandrel 402.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
541	2	22.4	3.2	2615054132	8710364010523

2. Aluminum Oxide Grinding Stones



911

932

952

953

997

8153

8175

8193

8215

Use on metals, castings, welded joints, rivets and rust. Ideal for sharpening, deburring and general purpose grinding of most materials.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
911	1	11.1	3.2	2615091132	8710364008056
932	1	9.5	3.2	2615093232	8710364007455
952	1	9.5	3.2	2615095232	8710364007462
953	1	6.4	3.2	2615095332	8710364007479
997	1	3.4	3.2	2615099732	8710364007486
8153	1	4.8	3.2	2615815332	8710364008124
8175	1	9.5	3.2	2615817532	8710364008131
8193	1	15.9	3.2	2615819332	8710364007493
8215	1	25.4	3.2	2615821532	8710364008148

Grinding / Sharpening

3. Silicon Carbide Grinding Stones



Designed to work well on stone, glass, ceramics, porcelain and non-ferrous metals.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
83142	1	7.0	3.2	2615314232	8710364016815
83322	1	3.2	3.2	2615332232	8710364016808
83702	1	3.2	3.2	2615370232	8710364016792
84922	1	4.8	3.2	2615492232	8710364016860
85422	1	19.8	3.2	2615542232	8710364016853
85602	1	10.3	3.2	2615560232	8710364016846

4. Abrasive Points




Use for finishing work and light deburring. For paint and rust removal without removing any of the base material.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
516	1	13.0	3.2	2615051632	8710364015238
518	1	13.0	3.2	2615051832	8710364015245

Cleaning / Polishing

3. Polishing Wheels



Ideal for polishing metals and plastics. Using polishing compound no. 421 with wheels produces a high luster. Use 414, 422 and 429 with mandrel 401. Use 423 and 425 with mandrel 402.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
414	6	13.0	3.2	2615041432	8710364007141
422	1	10.0	3.2	2615042232	8710364007158
423	1	26.0	3.2	2615042332	8710364007165
429	1	26.0	3.2	2615042932	8710364007189
425	1	22.5	3.2	2615042532	8710364007172
421	1			2615042132	8710364008452

4. Bristle Brushes



Use for light deburring, cleaning, polishing of silverware, jewellery and other precious metals. Can be used with polishing compound (421).



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
403	1	19.0	3.2	2615040332	8710364007127
404	1	13.0	3.2	2615040432	8710364007134
405	1	3.2	3.2	2615040532	8710364008230

Cutting

1. DREMEL® SpeedClic®




Dremel, the inventor of the Multitool, now brings you SpeedClic - an innovation that makes changing cut-off wheels quick and easy. Through a patented mandrel and wheel design, Dremel has found a way that enables you to change your accessory in 3 simple steps - Pull, Click, Twist - without using any tools. The Starter Set SC406 includes the new SpeedClic mandrel and two SpeedClic cut-off wheels. The fiberglass reinforced cut-off wheels SC426 are replacement cut-off wheels specifically for the SpeedClic system.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
SC406	1+2	32.0	3.2	2615S406JA	8710364033461
SC426	5	32.0	3.2	2615S426JA	8710364033478

2. Cut-Off Wheels



For slicing and cutting in metal, wood and plastic. Cut-off wheels make it easy to cut or slot bolts, screws, sheet metal, thin wood and plastic. Fiberglass reinforced cut-off wheels (456, 426, 426B) are for tough applications. The cut-off wheel cuts only along its edge. Do not attempt to sand or cut curved holes with them. Use Dremel cut-off wheels with mandrel 402.



Model	Quantity	Working ø mm	Shank ø mm	Ordernumber	EAN
426B	20	32.0	3.2	2615426BJA	8710364026296
456	10	38.0	3.2	26150456JA	8710364023011
426	5	32.0	3.2	2615042632	8710364007448
540	5	32.0	3.2	2615054032	8710364010516
420	20	24.0	3.2	2615042032	8710364007431
409	36	24.0	3.2	2615040932	8710364007424

Sanding

1. Sanding Bands



For rough shaping and smoothing wood and fiberglass, removing rust from metal surfaces and shaping rubber surfaces. Sanding bands are easily replaceable.



Model	Quantity	Working ø mm	Shank ø mm	Grit	Ordernumber	EAN
407	1	13.0	3.2	60	2615040732	8710364007226
408	6	13.0	3.2	60	2615040832	8710364007233
432	6	13.0	3.2	120	2615043232	8710364007264
430	1	6.4	3.2	60	2615043032	8710364007240
431	6	6.4	3.2	60	2615043132	8710364007257
438	6	6.4	3.2	120	2615043832	8710364007271
439	1	9.5	3.2	60	2615043932	8710364008391
440	6	9.5	3.2	60	2615044032	8710364008407
444	6	9.5	3.2	120	2615044432	8710364008414

2. Flapwheels



Perfect for sanding flat or contoured surfaces on metal, wood, rubber or plastic.



Model	Quantity	Working ø mm	Shank ø mm	Grit	Ordernumber	EAN
502	1	28.6	3.2	80	2615050232	8710364015252
504	1	28.6	3.2	80	2615050432	8710364015269