

Insulgrip® Wiring Devices

Watertight Safety-Shroud® Twist-Lock®

20 and 30 Amp

Plugs and Connectors



- Maintains UL Type 4X watertight seal when in use and when disconnected
- Recessed blades provide protection against bending and breaking
- Neoprene sealing gland and thermoplastic guard assure sealing when fully connected
- Catalog number and color-coded voltage are visible when in use for quick, easy identification

Receptacles



- One-step self latching spring-loaded cover ensures UL 4X watertight seal while not in use
- Available mechanical interlock maximizes user safety

Flanged Inlets



- High-impact thermoplastic housing for heavy-duty industrial environments
- Neoprene closure cap provides environmental seal when not in use for long-term reliability
- Accepts standard NEMA locking connector bodies for maximum flexibility



Watertight seals protect connections from washdown in food processing.



Chemical resistant thermoplastic construction withstands harsh environments found in wastewater treatment plants.



Maximum reliability and durability keeps mission-critical support systems up and running in military applications.

Ordering Information



| NEMA Rating | Color Coded by Voltage | | Poles and Wires | Plug | Connector | Flanged Inlet | Receptacle | |
|-------------|------------------------|--|-----------------|---------------|------------------|------------------|------------------|------------------|
| 20A | 125V | | L5-20 | 2-Pole 3-Wire | HBL2311SW | HBL2313SW | HBL2315SW | HBL2310SW |
| 20A | 250V | | L6-20 | 2-Pole 3-Wire | HBL2321SW | HBL2323SW | HBL2325SW | HBL2320SW |
| 20A 3Ø | 250V | | L15-20 | 3-Pole 4-Wire | HBL2421SW | HBL2423SW | HBL2425SW | HBL2420SW |
| 20A 3Ø | 480V | | L16-20 | 3-Pole 4-Wire | HBL2431SW | HBL2433SW | HBL2435SW | HBL2430SW |
| 30A | 125V | | L5-30 | 2-Pole 3-Wire | HBL2611SW | HBL2613SW | HBL2615SW | HBL2610SW |
| 30A | 250V | | L6-30 | 2-Pole 3-Wire | HBL2621SW | HBL2623SW | HBL2625SW | HBL2620SW |
| 30A | 125/250V | | L14-30 | 3-Pole 4-Wire | HBL2711SW | HBL2713SW | HBL2715SW | HBL2710SW |
| 30A 3Ø | 250V | | L15-30 | 3-Pole 4-Wire | HBL2721SW | HBL2723SW | HBL2725SW | HBL2720SW |
| 30A 3Ø | 480V | | L16-30 | 3-Pole 4-Wire | HBL2731SW | HBL2733SW | HBL2735SW | HBL2730SW |