

## Cable housing - KGS-MSTB 2,5/20 - 1805615

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable housing, pitch: 0 mm, number of positions: 20, dimension a: 100 mm, color: green

The figure shows an 8-position version



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 046620
GTIN	4017918046620
Weight per Piece (excluding packing)	28.750 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

Width [ w ]	19.8 mm
Height [ h ]	55.8 mm
Pitch	0.00 mm
Dimension a	100 mm

#### General

Range of articles	KGS-MSTB 2,5
Number of positions	20
Insulating material group	I
Insulating material	ABS
Flammability rating according to UL 94	HB

### Standards and Regulations

# Cable housing - KGS-MSTB 2,5/20 - 1805615

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000437
ETIM 6.0	EC000437

### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Cable housing - KGS-MSTB 2,5/20 - 1805615

### Approvals

#### Approval details


EAC		B.01742
-----	---	---------

### Accessories

#### Accessories

##### Cable housing

Cable housing - KGS-MSTB 2,5/ DST - 1784914



Transparent label carrier, can be marked with marker strips SBS 2.5/7.5

---

### Terminal marking

Marker for terminal blocks - SBS 2,5/7,5 - 1007604



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, perforated, mounting type: snap into tall marker groove, snap into flat marker groove, for terminal block width: 7.5 mm, lettering field size: 15 x 7.5 mm

---

Accessories - KD-KGS-MSTB - 1804658



Molded cable strain relief, suitable for KGS-... cable housings, prevents the cable from being bent