

Front adapters - FLKM 50-PA-MODI-TSX/Q - 2294306

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


VARIOFACE front adapter, for Schneider Electric MODICON TSX Quantum, 1 x 32 channels can be connected



The illustration shows versions
FLKM 50-PA-MODI-TSX/Q and
FLKM 50/ 4-FLK14/PA-MODI-TSX/
Q



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 132699
Weight per Piece (excluding packing)	200.84 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)
	4 A (per connection, supply via separate power supply)
Channels which can be connected	32
Connection type, connector	IDC/FLK pin strip (2.54 mm)
Number of connectors	1
No. of positions, connector	50
Number of positions	50
Mounting position	any
Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103
Rated surge voltage / insulation	0.6 kV / Basic isolation

Front adapters - FLKM 50-PA-MODI-TSX/Q - 2294306

Technical data

General

Rated insulation voltage	63 V
Pollution degree	2
Surge voltage category	II

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Supported controller

Control	Schneider Electric MODICON TSX QUANTUM
- suitable I/O card	DDI 353
	DDI 841
	DDI 853
	DAI 340
	DAI 353
	DAI 440
	DAI 453
	DDO 353
	DDM 390
	ACI 030
	ACI 040
	ATI 030
	ARI 030
	AVI 030
	ACO 020
	ACO 130
	AVO 020
	EHC 105
	EHC 202

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

Front adapters - FLKM 50-PA-MODI-TSX/Q - 2294306

Classifications

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC001423
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details


UL Recognized

cUL Recognized

GOST


Front adapters - FLKM 50-PA-MODI-TSX/Q - 2294306

Approvals

cULus Recognized 

Drawings

Circuit diagram



Connection scheme FLKM 50-PA-MODI-TSX/Q