

## Marker for terminal blocks - UC-TM 5 GN - 0818315

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



Marker for terminal blocks, Sheet, green, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.2 mm, Lettering field: 10.5 x 4.6 mm

### Why buy this product

- ✓ The UC-TM ... UniCard labeling range includes markers for products with tall marker grooves
- ✓ The multi-section marking strips are easy to fit and can be easily separated if required
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The markers support multi-line labeling



### Key commercial data

|                                      |                                                                                      |
|--------------------------------------|--------------------------------------------------------------------------------------|
| Packing unit                         | 10 pc                                                                                |
| Minimum order quantity               | 10 pc                                                                                |
| GTIN                                 |  |
| Weight per Piece (excluding packing) | 11.44 g                                                                              |
| Custom tariff number                 | 39269097                                                                             |
| Country of origin                    | Poland                                                                               |
| Note                                 | Made to Order (non-returnable)                                                       |

### Technical data

#### Dimensions

|           |      |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|       |                         |
|-------|-------------------------|
| Note  | Can be labeled with CMS |
| Color | green                   |

## Marker for terminal blocks - UC-TM 5 GN - 0818315

### Technical data

#### General

|                                         |                                |
|-----------------------------------------|--------------------------------|
| Components                              | free from silicone and halogen |
| Inflammability class according to UL 94 | V2                             |
| Material                                | PA                             |
| Wipe resistance                         | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels             | 96                             |
| Number of individual labels per row     | 12                             |
| Marking mounting type                   | Snap into tall marker groove   |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### Accessories

Accessories

Magazine

## Marker for terminal blocks - UC-TM 5 GN - 0818315

### Accessories

Magazine - P1 UC-MAG 1 - 5146079



Magazine, for CMS-P1-PLOTTER, for accommodating UC-TM..., UC-TMN..., UC-WMC 3,1..., UC-WMTBA...

---

Phoenix Contact 2015 © - all rights reserved  
<http://www.phoenixcontact.com>