



Wahlweise mit
Frontplatte

Modell	L	L1	B	B1	H	H1	E	E1	F	F1	D	K	l1	l2	M	N	Wahlweise mit Frontplatte
EG 1030	100	95	54	49	30	25	66	66	39	39	/	/	27	17	37 ^{+0.2} _{-0.1}	24 ^{+0.2} _{-0.1}	
EG 1040	100	95	54	49	40	35	66	66	39	39	/	/	27	17	37 ^{+0.2} _{-0.1}	24 ^{+0.2} _{-0.1}	
EG 1230	125	117.8	67	59.8	30	24	97	86	39	48	105	30	29	21	50 ^{+0.2} _{-0.1}	40 ^{+0.2} _{-0.1}	
EG 1240	125	117.8	67	59.8	40	34	97	86	39	48	105	30	29	21	50 ^{+0.2} _{-0.1}	40 ^{+0.2} _{-0.1}	X
EG 1250	125	117.8	67	59.8	50	44	97	86	39	48	105	30	29	21	50 ^{+0.2} _{-0.1}	40 ^{+0.2} _{-0.1}	X
EG 1530	150	142.8	82	74.8	30	24	122	116	54	63	130	40	34	21	65 ^{+0.3} _{-0.2}	55 ^{+0.3} _{-0.2}	
EG 1545	150	142.8	82	74.8	45	39	122	116	54	63	130	40	34	21	65 ^{+0.3} _{-0.2}	55 ^{+0.3} _{-0.2}	X
EG 1560	150	142.8	82	74.8	60	54	122	116	54	63	130	40	34	21	65 ^{+0.3} _{-0.2}	55 ^{+0.3} _{-0.2}	X
EG 2030	200	192.8	112	104.8	30	24	172	153.7*	84	88.9	180	4.4	36	36	95 ^{+0.4} _{-0.2}	97.4 ^{+0.4} _{-0.2}	
EG 2050	200	192.8	112	104.8	50	44	172	153.7*	84	88.9	180	4.4	36	36	95 ^{+0.4} _{-0.2}	97.4 ^{+0.4} _{-0.2}	X
EG 2070	200	192.8	112	104.8	70	64	172	153.7*	84	88.9	180	4.4	36	36	95 ^{+0.4} _{-0.2}	97.4 ^{+0.4} _{-0.2}	X

* = 7mm über Mitte nach oben

Maßstab: 1:1

Zchn.Nr: 1K 5010.352.03

Artikel:ELEGANT
Größe I-IV ohne GWDBU
Katalogzeichnung

BOPLA
A Pleuro Pleuro Company

3627 36 08 2889
Ae.Nr. Datum: 05.08.93 OK