

# CONDUCTIVE BOXES + SMD-BOXES

**CONDUCTIVE BOXES** (new organization system for EGB laboratories)

**ALU RAILS** (diverting)  
**AS 50 ESD**  
**AS 100 ESD**

**A4-18 PLATTE1-6-10**  
**A4-16 PLATTE1-6-10**

**MAGNETIC PINS**  
**R 30 ESD**   **R 40 ESD**  
**Q 40 ESD**   **D 40 ESD**

**CLIP**  
**DC1 ESD**

**HOOKS**

conductive material

|                    |                    |                    |
|--------------------|--------------------|--------------------|
| Art. No.           | <b>A 4-18-6-10</b> | <b>A 4-16-6-10</b> |
| Outside dimensions | 160 x 210 x 82     | 240 x 210 x 82     |
| Inside dimensions  | 126 x 178 x 79     | 208 x 178 x 79     |
| Colours            | ●                  | ●                  |

## CONDUCTIVE BOXES + SUBDIVISIONS



|               |                   |
|---------------|-------------------|
| Art. No.      | <b>A 4-1-6-10</b> |
| Base area     | 175 x 100         |
| Top edge      | 250 x 125         |
| Height inside | 34 mm             |
| Colours       | ●                 |



|               |                   |
|---------------|-------------------|
| Art. No.      | <b>A 4-2-6-10</b> |
| Base area     | 190 x 120         |
| Height inside | 50 mm             |
| Colours       | ●                 |



|               |                   |
|---------------|-------------------|
| Art. No.      | <b>A 4-3-6-10</b> |
| Base area     | 210 x 150         |
| Top edge      | 260 x 200         |
| Height inside | 40 mm             |
| Colours       | ●                 |



|                    |                     |
|--------------------|---------------------|
| Art. No. (a)       | <b>A 4-4 N-6-10</b> |
| Art. No. (b)       | <b>A 4-70-6-10</b>  |
| Outside dimensions | 260 x 165           |
| Height outside (a) | 45                  |
| Height outside (b) | 70                  |
| Colours            | ●                   |

## PORTABLE RACK, CHROME-PLATED FOR 8 OR 10 TRAYS



|                    |   |   |
|--------------------|---|---|
| Art. No.           | <b>A 4-4 ESD TRAY</b>   | <b>A 4-70 ESD TRAY</b>                                      |
| Outside dimensions | 610 x 190 x 252   | 610 x 190 x 252   |
| Note               | Portable rack, chrome-plated for 10 trays <b>A 4-4 N-6-10</b> | Portable rack, chrome-plated for 8 trays <b>A 4-70-6-10</b> |