



GE  
Lighting

54  
kWh/1000h

A  
energy class

100  
lumens/watt

## T5 LongLast™ - High Output, G5 Cap

FT5/49W/835/GE/LL/SL1/30

# 61121




### Product information

T5 LongLast™ lamps are triphosphor fluorescent lamps with 16mm outer diameter (5/8 of an inch). These lamps feature “Starcoat™ Technology” that delivers high quality triphosphor performance. GE produces two ranges of T5 LongLast™ lamps in 4 different lengths:

- High Efficiency offering high lumens per watt
- High Output offering improved lumen package

### Application areas

- Retail
- Office
- Education
- Industrial



WORLDWIDE PARTNER

## Product data

Product Code	61121
Bulb Shape	Tubular
Bulb Diameter [mm]	16
Regulatory comment	EUP related
Bulb maximum overall diameter [mm]	16
Cap to Cap Length (Max) [mm]	1449
Net weight per piece [g]	125
Gross weight per piece [g]	160
Mercury Content [mg]	2.5
UV radiance	Exempt
Brand	General Electric (GE)
Cap/Base	G5

## Performance data

Colour Code	835
Lumen at 25°C [lm]	4450
Weighted energy consumption [kWh/1000h]	53.84
Rated efficacy [lm/W]	99
Energy efficiency class (EEC)	A
Rated Life [h]	30000
Rated median life on electronic (HF / ECG) ballast on IEC 36000 12-hour cycle	
Rated median life on electronic (HF / ECG) ballast on IEC 30000 3-hour cycle	
Nominal correlated colour temperature (CCT) [K]	3500
Nominal lumens [lm]	4900
Colour Rendering Index (CRI) [Ra]	85


## Electrical data

Design Ambient Temperature [°C]	35
Design Lamp ambient temperature [°C]	35
Starting ambient temperature range	-15
Dimming Capability	Yes
Nominal power [W]	49


## Logistic data

DUN Code	10043168611210
EAN Code	0043168902793
Pack Quantity	30
Inner pack type	SLEEVE
Outer pack type	OUTER BOX
Layer quantity	210 Special
Pallet quantity EUR (PC)	1520
Pallet quantity UK (PC)	2000
Outer case size	1490 x 120 x 102 (mm)
Product status	Available


## Technical drawing




## Lumen maintenance data



## Survival data



## Service life data



## Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Linear Fluorescent Lamps Catalogue \(PDF\)](#)

[LFL T5 LongLast™ Lamps - Data sheet \(EN\) \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

[High-res images / Technical drawings \(HTTP\)](#)

[Certificate for the Quality Management System of GE Lighting EMEA \(PDF\)](#)

[Certificate for the Environmental Management System of GE Lighting EMEA \(PDF\)](#)