

Super Ferritic Clamps



The Supra Ferritic Clamp is a superior clamp to the quality Gold clamp with the added advantage of being a Stainless Steel band with a Carbon Steel, Zinc Plated bolt.

Unlike Super, all components are retained when the bolt is removed, thus facilitating ease of use with conventional assembly and automated tools. It has gained acceptance in those application areas where a band of Stainless Steel is required over Plated Carbon Steel but not with the associated costs of a full Stainless Steel clamp.

It has bevelled edges to reduce wear and tear to the hose.

The band bridge protects and reinforces the articulated tensioning system. Recommended torque tightening values and working pressures are published and are available.

Applications:

Commonly used in hose assembly manufacturing, agriculture, hydraulics, general engineering, chemical and food processing industries.

Sizes Available:

17-252mm.

Code	Description
SC239-252-SUF	Supra Clamp 239-252 mm Ferritic
SC226-239-SUF	Supra Clamp 226-239 mm Ferritic
SC213-226-SUF	Supra Clamp 213-226 mm Ferritic
SC200-213-SUF	Supra Clamp 200-213 mm Ferritic
SC187-200-SUF	Supra Clamp 187-200 mm Ferritic
SC174-187-SUF	Supra Clamp 174-187 mm Ferritic
SC162-174-SUF	Supra Clamp 162-174 mm Ferritic
SC150-162-SUF	Supra Clamp 150-162 mm Ferritic
SC140-150-SUF	Supra Clamp 140-150 mm Ferritic
SC130-140-SUF	Supra Clamp 130-140 mm Ferritic
SC121-130-SUF	Supra Clamp 121-130 mm Ferritic
SC112-121-SUF	Supra Clamp 112-121 mm Ferritic
SC104-112-SUF	Supra Clamp 104-112 mm Ferritic
SC97-104-SUF	Supra Clamp 97-104 mm Ferritic
SC91-97-SUF	Supra Clamp 91-97 mm Ferritic
SC85-91-SUF	Supra Clamp 85-91 mm Ferritic
SC79-85-SUF	Supra Clamp 79-85 mm Ferritic
SC73-79-SUF	Supra Clamp 73-79 mm Ferritic
SC68-73-SUF	Supra Clamp 68-73 mm Ferritic
SC63-68-SUF	Supra Clamp 63-68 mm Ferritic
SC59-63-SUF	Supra Clamp 59-63 mm Ferritic
SC55-59-SUF	Supra Clamp 55-59 mm Ferritic
SC51-55-SUF	Supra Clamp 51-55 mm Ferritic
SC47-51-SUF	Supra Clamp 47-51 mm Ferritic
SC43-47-SUF	Supra Clamp 43-47 mm Ferritic
SC40-43-SUF	Supra Clamp 40-43 mm Ferritic
SC37-40-SUF	Supra Clamp 37-40 mm Ferritic
SC34-37-SUF	Supra Clamp 34-37 mm Ferritic