

## General Information

Extended Product Type:	216RS4
Product ID:	2CMA193097R1000
EAN:	7392696930970
Catalog Description:	Surface socket-outlet, 4h, 16A, IP44, 2P+E
Long Description:	Surface socket-outlet, earthing sleeve position 4h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Yellow

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

## Ordering

EAN:	7392696930970
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

## Dimensions

Product Net Width:	91 mm
Product Net Height:	66 mm
Product Net Length:	117 mm
Product Net Depth:	117 mm
Product Net Weight:	0.22 kg

## Container Information

Package Level 1 Width:	143 mm
Package Level 1 Length:	397 mm
Package Level 1 Height:	187 mm
Package Level 1 Gross Weight:	0.24 kg
Package Level 1 EAN:	7392696930970
Package Level 1 Units:	10 piece

## Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

## Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

## Additional Information

Additional Information:	Cable entry, flexible membrane and metric threaded M20 insert for top cable entry.Rear knock-out cable entry.
Cable Cross-Section:	1.5 ... 4 mm <sup>2</sup>
Color:	Yellow
Degree of Protection:	acc. to IEC 60529 IP44
Enclosure Material:	Thermoplastic
Frequency (f):	50 Hz 60 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216RS4
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	RS
Product Name:	Industrial Socket Outlet
Protection Type:	Splashproof
Rated Current (I <sub>n</sub> ):	16 A
Rated Voltage (U <sub>r</sub> ):	100 ... 130 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2

Suitable For: Surface Socket Outlets  
Suitable for Product Class: Industrial Plugs and Sockets

**Classifications**

E-nummer: 2416442

UNSPSC: 39120000

